

Part Number: [0039000078](#)
Status: Active
Overview: [Mini-Fit Jr. Power Connectors](#)
Description: Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, 16 AWG, Bag

Documents:

图纸 (PDF)	包装规格 PK-5556-003-001 (PDF)
产品规格 PS-5556-001-001 (PDF)	测试总结 55560010-TS-000 (PDF)
产品规格 PS-5556-002-001 (PDF)	测试总结 TS-5556-002-001 (PDF)
应用规范 55560001-AS-000 (PDF)	RoHS 证书



一般应用	Power, 线对板, 线对线
Crimp Quality Equipment	Yes
概述	Mini-Fit Jr. Power Connectors
备用包装	39000077 (Reel)
产品名称	Mini-Fit
UPC	800753727021
物理	
耐用性(插拔次数) - 最多次数	30
部件属性	母端
材料-金属	黄铜
材料-接合处电镀	锡
材料-终端电镀	锡
Net Weight	135.300/mg
包装形式	袋
最薄镀层 - 接合部位	0.889#m
最小镀层: 端接	0.889#m
终端界面: 类型	压接或压缩
导线绝缘直径	1.80-3.10mm
线径规格 AWG	16
线缆尺寸mm#	N/A
电气	
每触点最大电流	9.0A
电压 - 最大	600V
材料信息	
Engineering Number	5556T3L
参考: 图纸编号	
应用规范	55560001-AS-000
包装规格	PK-5556-003-001
产品规格	PS-5556-001-001, PS-5556-002-001
销售用图纸	55560000-SD-000
测试总结	55560010-TS-000, TS-5556-002-001

EU ELV
Not Relevant

EU RoHS China RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit
[Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series
[5556 Series](#)

Use With

Mini-Fit Jr. Receptacle Housing [5557](#)

Mini-Fit BMI Slide and Lock Panel
Mount [44516](#)
Mini-Fit BMI Panel
Mount Receptacle Housing
 [42474](#) ,
[43760](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
-------------	-----------

Extraction Tool	11030044
Hand Crimp Tool for	2002182200
Mini-Fit Jr. Male and Female Crimp Terminals, 16 AWG	
Japan	

Description	Product #
Hand Crimp Tool	<u>570225300</u>
New Handtool (Straight Action)	<u>570225400</u>
Hand Extraction Tool	<u>570316000</u>

This document was generated on 07/16/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION