

# WP-G PP HF PG7 - Protective hose screw connection



3240988

<https://www.phoenixcontact.com/gb/products/3240988>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable gland made from PP with Pg thread, IP65 protection



## Commercial data

Item number	3240988
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AF7DSA
Product key	AF7DSA
Catalog page	Page 594 (C-3-2019)
GTIN	4046356711203
Weight per piece (including packing)	3.85 g
Weight per piece (excluding packing)	3.85 g
Customs tariff number	39174000
Country of origin	DE

# WP-G PP HF PG7 - Protective hose screw connection



3240988

<https://www.phoenixcontact.com/gb/products/3240988>

## Technical data

### Product properties

Product type	Protective hose screw connection
Application	Cable gland
Type	Outer thread
Cable outlet	straight
Thread type	Pg

### Dimensions

Width	20 mm
Height	40 mm
Wrench size	16 mm
Wrench size for mounting	16 mm
	18 mm

### Material specifications

Material	PP
Flammability rating according to UL 94	HB
Material for screw connection	PP
Components	halogen-free

### Cable/line

Halogen-free	yes
--------------	-----

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-10 °C ... 110 °C

# WP-G PP HF PG7 - Protective hose screw connection



3240988

<https://www.phoenixcontact.com/gb/products/3240988>

## Approvals

💡 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3240988>



VDE approval of drawings

# WP-G PP HF PG7 - Protective hose screw connection



3240988

<https://www.phoenixcontact.com/gb/products/3240988>

## Classifications

### ECLASS

ECLASS-13.0	27430311
-------------	----------

### ETIM

ETIM 9.0	EC001178
----------	----------

### UNSPSC

UNSPSC 21.0	39121300
-------------	----------

# WP-G PP HF PG7 - Protective hose screw connection



3240988

<https://www.phoenixcontact.com/gb/products/3240988>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)