

## Features

- Durable and easy to install on both existing and new-build steps.
- A hard wearing, gritty surface available in bright colours helps protect against slips and trips whilst meeting the Equality Act requirements (DDA).
- Manufactured with chamfered back edge for additional safety.
- Fire Tested to: DIN 13501: Bfl - s1 (2018) & EN ISO 11925-2:2020 & EN ISO 9239-1:2010 (both 2021).
- Slip Tested to: DIN 51130 - R13 & BS 7976-2 - low slip potential.

## RS PRO Stair Nosing - Yellow

### 3m x 55mm x 55mm

RS Stock No.: 0712637



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

- Durable and easy to install on both existing and new-build steps.
- A hard wearing, gritty surface available in bright colours helps protect against slips and trips whilst meeting the Equality Act requirements (DDA).
- Manufactured with chamfered back edge for additional safety.
- Fire Tested to: DIN 13501: Bfl - s1 (2018) & EN ISO 11925-2:2020 & EN ISO 9239-1:2010 (both 2021).
- Slip Tested to: DIN 51130 - R13 & BS 7976-2 - low slip potential

## General Specifications

<b>Size</b>	3 m x 55 mm x 55 mm
<b>Product Height</b>	5 mm
<b>Colour</b>	Yellow
<b>Weight (kg)</b>	1.8
<b>Material</b>	GRP
<b>Surface Finish</b>	Quartz grit
<b>Min. Operating Temperature</b>	-50°C
<b>Max. Operating Temperature</b>	+90°C
<b>Environmental Resistance</b>	Suitable for indoor and outdoor environments
<b>Typical Applications</b>	External steps
<b>Installation Method</b>	Bond or screw to surface
<b>Cleaning Method</b>	Product should be almost maintenance free in most outside environments. Natural elements will have the effect of cleaning the product. Brushing and flushing with a mild detergent solution may be desirable now and again to restore appearance.

## Approvals

<b>Fire Tested to</b>	DIN 13501: Bfl - s1 (2018) & EN ISO 11925-2:2020 & EN ISO 9239-1:2010 (both 2021)
<b>Slip Tested to</b>	DIN 51130 - R13 & BS 7976-2 - low slip potential

## Similar Products

Stock No.	Brand	Product Name	Size	Colour	Weight (kg)
0712633	RS PRO	Stair Nosing	3 m x 55 mm x 55 mm	Black	1.8
0712634	RS PRO	Stair Nosing	1.5 m x 55 mm x 55 mm	Black	0.9
0712635	RS PRO	Stair Nosing	3 m x 55 mm x 55 mm	Black/Yellow	1.8
0712636	RS PRO	Stair Nosing	1.5 m x 55 mm x 55 mm	Black/Yellow	0.9
0712638	RS PRO	Stair Nosing	1.5 m x 55 mm x 55 mm	Yellow	0.9