



Foot protection

MONTBRUN S3 SRC

CONSTRUCTION

Robust low-cut shoe for the construction industry, with a wider fit and robust construction



Specific benefits



Comfort

- Stabilisation of the foot when walking
- Shock-absorbing heel to relieve joint strain
- Wide shape to accommodate stronger foot morphologies



Performance

- High stability ensured by the sole's grip properties



Hygiene

- Removable insock for easy cleaning

Certifications and norms



EN ISO 20345

S3 WRU FO A E SR

Applications

- Public works
- Building
- Finishing works / Craftsmanship
- Light industry
- Maintenance
- Automotive

Protects against risks



Antistatic



Shock



Slip



Perforation



Foot protection

MONTBRUN S3 SRC

CONSTRUCTION

Robust low-cut shoe for the construction industry, with a wider fit and robust construction

Standards - Details

Technical details

Shoe type	Low shoe
Outsole material	PU, 2d
Anti-perforation insert	Stainless steel
Upper material	Leather
Upper finition material	Croupon, Water repellent
Safety toe-cap	Stainless steel
Lining material	Textile, Polyamid
Footbed material	EVA, Polyamide
Footbed characteristic	Removable, Breathable, Pre-molded
Outsole finition	Injected
Weight (g per shoe)	702
Size range	39 → 48



Safety footwear

MONTBRUN S3 SRC

CONSTRUCTION

Robust low-cut shoe for the construction industry, with a wider fit and robust construction

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
MONTBS3NO39	Black	39	MONTBRUN S3 SRC	3295249100636	13295249100633	5	1	8.0 kg	61.0 cm	34.0 cm	23.0 cm
MONTBS3NO40	Black	40	MONTBRUN S3 SRC	3295249100643	13295249100640	5	1	8.5 kg	23.0 cm	59.8 cm	34.0 cm
MONTBS3NO41	Black	41	MONTBRUN S3 SRC	3295249100650	13295249100657	5	1	8.8 kg	23.2 cm	60.6 cm	34.4 cm
MONTBS3NO42	Black	42	MONTBRUN S3 SRC	3295249100667	13295249100664	5	1	8.0 kg	61.0 cm	34.0 cm	23.0 cm
MONTBS3NO43	Black	43	MONTBRUN S3 SRC	3295249100674	13295249100671	5	1	10.0 kg	68.2 cm	36.0 cm	25.0 cm
MONTBS3NO44	Black	44	MONTBRUN S3 SRC	3295249100681	13295249100688	5	1	9.5 kg	25.0 cm	64.0 cm	35.4 cm
MONTBS3NO45	Black	45	MONTBRUN S3 SRC	3295249100698	13295249100695	5	1	9.8 kg	25.6 cm	64.2 cm	35.6 cm
MONTBS3NO46	Black	46	MONTBRUN S3 SRC	3295249100704	13295249100701	5	1	10.4 kg	25.2 cm	65.0 cm	36.4 cm
MONTBS3NO47	Black	47	MONTBRUN S3 SRC	3295249100711	13295249100718	5	1	10.9 kg	25.0 cm	64.6 cm	37.0 cm
MONTBS3NO48	Black	48	MONTBRUN S3 SRC	3295249100728	13295249100725	5	1	11.4 kg	24.4 cm	64.8 cm	37.0 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height