


14074 DZH-63-25-PPV-A Flat cylinder - Series: All



14074 DZH-63-25-PPV-A Flat cylinder - Series: All

Pos.	Part no.	Type	Note	Qty.	Unit
A	108709	DZH- 63-PPV-A Set of wearing parts	Spare parts: 2, 8, 11, 14, 15, 24, 25	1	PC
1	200127	DIN 439-B-M16X1,5-04 Hex nut		1	PC
2	229860	WIFC2-20X30X10,7-TPE-U Wiper seal	Grease using during assembly. See position 24	1	PC
3		SINT-B50 20X26X23 Cylinder bearing	Not available separately, see position 9	1	PC
4		DZH-63-PPV Bearing cap module	Not available separately, see position 9	1	PC
5		B-6X1-N-NBR75 O-ring ISO3601	Not available separately, see position 9+23	2	PC
6		RG4 6X8X19.7X5 adjusting screw	Not available separately, see position 9+23	2	PC
7		DNC- 63/80 Threaded sleeve	Not available separately, see position 9+23	2	PC
8		DIFC1-25X33X7,8-TPE-U Buffer seal	Not available separately, see position 9+23+999 Grease using during assembly. See position 24	2	PC
9	760701	DZH-63-PPV:SP Bearing cap module		1	PC
10	240709	M 7X48,5 DZH-50/63 flange screw	Use locking compound. See position 25 Tightening torque 15 Nm / 11.1 lbf ft	8	PC
11		B-65X2-N-NBR75 O-ring ISO3601	Not available separately, see position A Grease using during assembly. See position 24	2	PC
12		ARA-20-X0080,0-A1/A1G Piston rod	Not available separately, see position 20	1	PC
13		50/63 PPV Buffer sleeve	Not available separately, see position 20	2	PC
14		LEFO1-88/44X7-TPE-U Lip seal	Not available separately, see position A Grease using during assembly. See position 24	2	PC
15		DZH-63 Guiding band	Not available separately, see position A Grease using during assembly. See position 24	2	PC
16		DZH-63-PPVA-S6 Piston	Not available separately, see position 18	1	PC
17		6,1X6 Magnet	Not available separately, see position 18	1	PC
18		DZH-63-PPVA-S6 Piston	Not available separately, see position 20	1	PC
19		DNN-63-PPV Threaded coupling	Not available separately, see position 20 Tightening torque 8 Nm / 5.9 lbf ft Use locking compound. See position 25	1	PC
20	106976	DZH-63-X-PPV-A Piston rod module	When ordering please specify the stroke (see type plate)	1	PC
21		DZH-63-... Cylinder barrel	Not available Grease using during assembly. See position 24	1	PC
22		DZH-63-PPV:CO End cap	Not available separately, see position 23	1	PC
23	8217555	DZH-63-PPV:SP End cap module		1	PC
24	684474	LUB-KC1 SILIKONFREI 20ML Lubricating grease		1	PC
25	8181256	CYBERBOND TM44 TB1ML Adhesive bonding agent		1	PC