

FEATURES

- Both 290 mm and 550 mm height versions available
- 48 drawer versions suiting all your requirements
- Grey polypropylene (PP) <u>cabinet</u>
- Drawers
 manufactured from
 crystal clear
 polystyrene (PS)
- Galvanised steel shelves
- Temperature tolerance (-40 to +55°C)
- Self-adhesive labels supplied for each drawer
- Flexible and efficient storage

RS PRO 48 Drawer Storage Unit, PP, Width 69mm x Depth 175mm x Height 37mm

RS Stock No.: 909-6965



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Drawer Storage



Product Description

From RS PRO these plastic storage cabinets are ideal for all your everyday storage needs. They are built from a hard-wearing plastic, with galvanised steel shelves, making these units both durable and long lasting. They are ideal for storing all your small parts, as well as providing easy access

General Specifications

Drawers	48
Drawer Material	PP
Case Material	PP
Colour	Grey
Drawer size	69mm x Depth 175mm x Height 37mm
Available Accessories to purchased separately	Cross Divider V-01 (5 Pcs/drawer), Length Divider V-012 (1 Pc/drawer)
Drawer Type	L-01
Transparent Drawers	Yes
Tilt Drawers	No
Wall Mounted	No
Applications	Garages, Workshops, Warehouses, Factories

Mechanical Specifications

Overall Height	550mm
Overall Width	310mm
Overall Depth	180mm
Weight	4.6kg



Storage Drawer Dimensions

Storage Drawer Size (H x W x D)	Quantity Of Storage Drawer	Each Drawer Capacity
37mm x 69mm x 175mm	4 x 12	5kg

Operation Environment Specifications

Temperature Tolerance	-40°C to 55°C
-----------------------	---------------

Cabinet Size HxWxD(mm)	Drawer Type	No of Drawers in	Each Drawer External Size	Each Drawer Internal Size	RS Stock No		
Cabinet HxWxD(mm) HxWxD(mm) 290mm HIGH CABINETS							
290 x 310 x 180	L-00	30	37 x 55 x 175	32 x 47 x 146	9096934		
290 x 310 x 180	L-01	24	37 x 69 x 175	32 x 61 x 146	9096943		
290 x 310 x 180	L-02	12	37 x 138 x 175	32 x 128 x 146	9096946		
290 x 310 x 180	L-04	12	59 x 92 x 175	55 x 82 x 146	9096940		
290 x 310 x 180	L-06	4	59 x 277 x 175	55 x 266 x 146	9096959		
290 x 310 x 180	L-07	6	81 x 138 x 175	74 x 128 x 146	9096952		
550mm HIGH CABINETS							
550 x 310 x 180	L-00	60	37 x 55 x 175	32 x 47 x 146	9096956		
550 x 310 x 180	L-01	48	37 x 69 x 175	32 x 61 x 146	9096965		
550 x 310 x 180	L-02	24	37 x 138 x 175	32 x 128 x 146	9096968		
550 x 310 x 180	L-04	24	59 x 92 x 175	55 x 82 x 146	9096962		
550 x 310 x 180	L-06	8	59 x 277 x 175	55 x 266 x 146	9096971		
550 x 310 x 180	L-07	12	81 x 138 x 175	74 x 128 x 146	9096974		