

## Features

- Wheels: unit supported with wheels
- Air intake and outlet intake of humid air is from side and discharge from right side panel
- Filter is provided at inlet
- Compressor : rotary type is used with environmental friendly refrigerant R290
- Water tank : 6L
- Tank full indication unit will stop working if tank is full
- Timer: 24 hours

## RS PRO Portable Dehumidifier 20L R290

RS Stock No.: 0282846



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

RS PRO portable dehumidifier with 7 operating modes and has adjustable humidity levels, and digital adjustable relative humidity percentages between 30% and 80%. The dehumidifier automatically monitors conditions and adjusts to default. It has 2-speed fan adjustment for comfort levels.

### Main Features

- *Dehumidifier 20L*
- *Refrigerant R290*
- *Extract up to 20 liter of water per day*
- *Water level detection, automatically shut off when water full*
- *Up to 24 hours timer*
- *Automatic defrosting function*

## General Specifications

Moisture Extraction Rate	20L/day
Refrigerant Type	R290
Noise Level	42dB
Water Tank Capacity	6.0L
Plug Type	European/UK Plug
Convertor	European transformer to UK convertor plug
Series	Portable
Product Overall Size	37x 26.5x 59.5cm
Product Weight	13.90kgs
Material	Plastic housing
Wheels	4pcs

## Mechanical Specifications

Timer	24 hours
Automatic Defrosting	Include
Washable Air Filter	Include
Working Space	22-40m2

## Electrician

Rate Voltage	220-240V~ 50Hz
Wattage	400W
Humidity Extraction	20L/D(30degree C,RH80 %)
Air Volume	260m3/h
Compressor	Rotary type
Control Model	Electronic
Fan Speed	2

## Approvals

Compliance/Certifications	CE, RoHS
Declarations	REACH DoC

## Similar Products

Stock No.	Brand	Product Name	Moisture Extraction Rate	Water Tank Capacity	Product Dimension
<b>2866477</b>	RS PRO	Industrial Dehumidifier	50L/day	7.0L	48 x 45 x 65.5 cm
0282846	RS PRO	Portable Dehumidifier	20L/day	6.0L	37x 26.5x 59.5 cm
0160696	RS PRO	Portable Dehumidifier	300ml/day	0.6L	14.6 x 14.6 x 22.7 cm

European transformer to UK convertor plug

