

Base cover lateral H: 100 mm D: 400 mm



| Model                                        |                                |
|----------------------------------------------|--------------------------------|
| product brand name                           | SIVACON S4                     |
| product designation                          | Base covers                    |
| design of the product                        | Lateral                        |
| design of cabinet base element               | for standard frame             |
| Suitability                                  |                                |
| suitability for interaction cable assignment | No                             |
| suitability for use for outside use          | No                             |
| Appearance                                   |                                |
| RAL color number                             | sim. RAL 5020                  |
| color                                        | blue green basic               |
| product component                            | module incl. mounting material |
| • on delivery                                |                                |
| • ventilation                                | No                             |
| Mechanical Design                            |                                |
| height                                       | 100 mm                         |
| width                                        | 12 mm                          |
| depth                                        | 400 mm                         |
| installation width for cabinet installation  | 12 mm                          |
| installation depth for cabinet installation  | 400 mm                         |
| net weight                                   | 1.16 kg                        |
| material                                     | sheet-steel                    |
| material thickness                           | 1.5 mm                         |
| Approvals Certificates                       |                                |
| General Product Approval                     |                                |
| other                                        |                                |



[Miscellaneous](#)



[Miscellaneous](#)

|                              |                                                   |                                                   |
|------------------------------|---------------------------------------------------|---------------------------------------------------|
| other                        | Environment                                       |                                                   |
| <a href="#">Confirmation</a> | <a href="#">Environmental Con-<br/>firmations</a> | <a href="#">Environmental Con-<br/>firmations</a> |

| Further information          |
|------------------------------|
| Information on the packaging |

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ1010-4BA01>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ1010-4BA01>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8PQ1010-4BA01](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ1010-4BA01)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

---

last modified:

4/30/2025 

