




Labels for IT ties, IMP plates and Q-tags, thermal transfer

Helatag 892 (White)

These labels are specially tailored to the sizes used in the IT marking tie and IMP/IT as well as Q-tag range. The flexible material sticks to the marking tie or tag, even on rounded surfaces. Print with HellermannTyton's premium range of thermal transfer printers and ribbons for optimum print results. Using unique numbering, graphics or barcodes the labels give excellent asset identification possibilities. This solution produces professional marking of tubes, pipes, cables and other parts.


Features and benefits

- Suited to the slightly rough surfaces of Q-tags, IT ties and IMP/IT plates
- Adheres to rounded surfaces
- Rounded corners ensure better long term durability of adhesion
- White labels give excellent contrast



Identification ties and tags.

MATERIAL	Type 892, Vinyl (PVC), white (WH)
Operating Temperature	-40 °C to +80 °C
Curing Temperature	from 0 °C
Adhesive	Acrylic
Thickness of Foil	83 µm
Chem. Material Properties	Good resistance against water, oils and most solvents.
Recommended Ribbon Type	TT822OUT
Thermal Transfer Printer	TT430, TT4030



RoHS

TYPE	Width (W)	Height (H)	Width of Liner (WL)	Labels per Row	For Size	Pack Cont.	Colour	Article-No.
TAG18-07TD1-892-WH	18.0	7.0	24.0	1 pc.	IT18FL	5,000 pcs.	White (WH)	596-12253
TAG18-16TD1-892-WH	18.0	16.0	24.0	1 pc.	IMP1.5	2,500 pcs.	White (WH)	596-12254
TAG23-06TD1-892-WH	23.0	6.0	30.0	1 pc.	IT18R	5,000 pcs.	White (WH)	596-12255
TAG23-10TD1-892-WH	23.0	10.0	30.0	1 pc.	IT50R	5,000 pcs.	White (WH)	596-12256
TAG26-21TD2-892-WH	26.0	21.0	57.0	2 pcs.	IT50RD	2,500 pcs.	White (WH)	596-12257
TAG28-16TD1-892-WH	28.0	16.0	34.0	1 pc.	IT1, IMP2	2,500 pcs.	White (WH)	596-12258
TAG43-16TD1-892-WH	43.0	16.0	50.0	1 pc.	IMP2.5	2,500 pcs.	White (WH)	596-12259
TAG43-21TD1-892-WH	43.0	21.0	50.0	1 pc.	IT50RT	2,500 pcs.	White (WH)	596-12260
TAG43-41TD1-892-WH	43.0	41.0	50.0	1 pc.	IMP2.5W1.75	1,000 pcs.	White (WH)	596-12261
TAG52-10TD1-892-WH	52.0	10.0	58.0	1 pc.	IT50L	5,000 pcs.	White (WH)	596-12262
TAG63TD1-892-WH	63.5	38.1	70.0	1 pc.	QT7040R, QT7040S	1,000 pcs.	White (WH)	596-12263
TAG68-16TD1-892-WH	68.0	16.0	74.0	1 pc.	IMP3.5, QT7016R	2,500 pcs.	White (WH)	596-12264
TAG102-64TD1-892-WH	102.0	64.0	106.0	1 pc.	QT10065R	250 pcs.	White (WH)	596-12265

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.