

# Componex Mini-Meters - stock range


## Battery level / status Indicators




SR9



SP11



R365BT






R500BT

These rugged and reliable battery status meters are suitable for a wide range of applications. Using external resistors the required voltage range can be set. By adding a suitable zener diode it is possible to measure a particular voltage over a wider span of the meter scale.


| Order Code | Sensitivity<br>±20% | Resistance<br>±15% | Rec. Price £: | 1+ | 5+ | 10+ | 25+ | 50+ | 100+ |
|------------|---------------------|--------------------|---------------|----|----|-----|-----|-----|------|
| SR9        | 0-500 $\mu$ A       | 700 $\Omega$       |               |    |    |     |     |     |      |
| SP11       | 0-1mA               | 345 $\Omega$       |               |    |    |     |     |     |      |
| R365BT     | 0-250 $\mu$ A       | 700 $\Omega$       |               |    |    |     |     |     |      |
| R500BT     | 0-250 $\mu$ A       | 650 $\Omega$       |               |    |    |     |     |     |      |

- Minature and standard sizes
- Ideal for portable equipment
- Low cost solution
- Minimum depth
- Very robust
- Ex-stock availability




| Dimensions<br>mm | A     | B     | W                 | D     | H    | I     |
|------------------|-------|-------|-------------------|-------|------|-------|
| R365BT           | 40.00 | 40.00 | 21.5 x 36.5 x 3.0 | 20.00 | 8.00 | 12.50 |
| R500BT           | 55.00 | 47.50 | 50.0 x 28.0 x 3.0 | 18.50 | 7.00 | 14.00 |


## Edgewise level and balance Indicators



SV5





SW4



E35FCZ


E35F100



E35F10





SX3



SY2

- Compact edgewise design
- Professional appearance
- Low cost solution
- Easy to back light
- Minimum depth
- Ex-stock availability

A wide range horizontal and vertical edgewise meters with left, bottom and centre zero, providing low cost indication.



| Order Code | Sensitivity<br>±20% | Resistance<br>±15% | Rec. Price £: | 1+ | 5+ | 10+ | 25+ | 50+ | 100+ |
|------------|---------------------|--------------------|---------------|----|----|-----|-----|-----|------|
| SY2        | 0-200 $\mu$ A       | 600 $\Omega$       |               |    |    |     |     |     |      |
| SX3        | 100-0-100 $\mu$ A   | 600 $\Omega$       |               |    |    |     |     |     |      |
| SW4        | 0-250 $\mu$ A       | 600 $\Omega$       |               |    |    |     |     |     |      |
| SV5        | 100-0-100 $\mu$ A   | 600 $\Omega$       |               |    |    |     |     |     |      |
| E35F10     | 0-100 $\mu$ A       | 1750 $\Omega$      |               |    |    |     |     |     |      |
| E35F100    | 0-200 $\mu$ A       | 600 $\Omega$       |               |    |    |     |     |     |      |
| E35FCZ     | 100-0-100 $\mu$ A   | 600 $\Omega$       |               |    |    |     |     |     |      |

| Dimensions<br>mm | A     | B     | C     | D     | F     | H     | I    |
|------------------|-------|-------|-------|-------|-------|-------|------|
| SY2              | 36.00 | 18.20 | 17.80 | 12.40 | 28.50 | 15.20 | 4.50 |
| SX3              | 36.00 | 18.20 | 17.80 | 12.40 | 28.50 | 15.20 | 4.55 |
| SW4              | 54.00 | 22.00 | 35.20 | 15.20 | 49.00 | 25.50 | 7.00 |
| SV5              | 54.00 | 22.00 | 35.20 | 15.20 | 49.00 | 25.50 | 7.00 |
| E35F10           | 39.00 | 18.50 | 35.00 | 14.00 | 24.00 | 22.00 | 4.50 |
| E35F100          | 39.00 | 18.50 | 35.00 | 14.00 | 24.00 | 22.00 | 4.50 |
| E35FCZ           | 39.00 | 18.50 | 35.00 | 14.00 | 24.00 | 22.00 | 4.50 |

AVAILABLE FROM: NATIONAL DISTRIBUTORS OR DIRECT FROM ANDERS IN MULTIPLES OF 10 PCS AND SUBJECT TO A MOQ OF 50 PCS.

DVM\CMMP4B Revision 5 03/06/04

PAGE 4

**anders electronics plc** Bayham Place, London NW1 OEU UK  
Tel: +44 (0)20 7380 8167 Fax: +44 (0)20 7874 1908 <http://www.anders.co.uk>

Anders Electronics plc (Anders) does not warrant the accuracy or completeness of the information contained herein, the supply of products by Anders is subject to its standard terms and conditions of sale. Prior to concluding any agreement with Anders the customer should satisfy itself of the accuracy and completeness of the information contained herein and should notify to Anders any intended use of the product.  
[www.anders.co.uk](http://www.anders.co.uk) | [info@anders.co.uk](mailto:info@anders.co.uk)

