



My Alu USB Drive



- Sophisticated all-metal housing
- Durable and practical design
- USB SuperSpeed 5Gbps / USB 3.2 Gen 1 (also compatible with USB 2.0)
- Easily transfer files
- Large keyring loop
- 2 year limited warranty



The sleek all-metal MyAlu USB Flash Drive from MyMedia is the ideal companion to store and move files.

The sophisticated metal design combines durability and practicality to provide an elegant way to help keep your most important files safe and close by.

Operating at USB SuperSpeed 5Gbps (USB 3.2 Gen 1), MyAlu delivers fast transfer speeds of up to 80MB/s and write speeds of up to 5 times faster than standard USB 2.0 drives.





Part Number	Description	Interface	Capacity
69275	MyMedia Metal USB Drive USB 3.2 Gen 1 16GB	USB 3.2 Gen 1/USB A	16GB
69276	MyMedia Metal USB Drive USB 3.2 Gen 1 32GB	USB 3.2 Gen 1/USB A	32GB
69277	MyMedia Metal USB Drive USB 3.2 Gen 1 64GB	USB 3.2 Gen 1/USB A	64GB
69278	MyMedia Metal USB Drive USB 3.2 Gen 1 128GB	USB 3.2 Gen 1/USB A	128GB



General Information	
Enclosure Material	Zinc Alloy
Colour	Silver
System Requirements	
Operating System	Windows 10, 8, 7 / Mac OS X 10.4 or higher
USB Host Port	USB 3.2 Gen 1 (also compatible with USB 2.0 ports)
Operational Conditions	
Operating Temperature	0°C to 70°C
Storage Temperature	-25°C to 85°C
Operating Humidity	35% to 80%
Connections	
USB Interface	USB 3.2 Gen 1
USB Connector Type	USB-A

Shipping information:

Logistic Info		Dimensions	Weight (approx)	Units
PRODUCT	1 Product / Pack	39.7 mm (L) x 12.2 mm (W) x 7 mm (H)	9 grams	1
PACK	10 Packs / Inner Carton	90 mm (L) x 9 mm (W) x 123 mm (H)	16 grams	1
INNER CARTON	54 Inner / Outer Carton	100 mm (L) x 50 mm x (W) 130 mm (H)	190 grams	10
OUTER CARTON	6 Outer Cartons / Layer	330 mm (L) x 300 mm x (W) 420 mm (H)	11.06 Kg	540
PALLET	4 Layers / Pallet	800 mm (L) x 1200 mm (W) x 1450 mm (H)	270 KG	12 960

Part Number	Barcode		EAN 128	EAN 14
69275	023942692751	Inner Outer	(02)00023942692751(37)10(91)483 (02)00023942692751(37)0540(91)483	20023942692755 50023942692756
69276	023942692768	Inner Master	(02)00023942692768(37)10(91)483 (02)00023942692768(37)0540(91)483	20023942692762 50023942692763
69277	023942692775	Inner Master	(02)00023942692775(37)10(91)483 (02)00023942692775(37)0540(91)483	20023942692779 50023942692770
69278	023942692782	Inner Master	(02)00023942692782(37)10(91)483 (02)00023942692782(37)0540(91)483	20023942692786 50023942692787