

00 21 19 LB E

KNIPEX L-BOXX® Electric 65-part



- Equipped with 65 brand name quality tools, some VDE-tested according to DIN EN 60900
- Several boxes can be securely joined together
- Flexible inner partitions
- With two-part tool holder made of hard-wearing polyester fabric
- Tool holders are connected to each other using hook-and-loop
- Handle can be lowered into a hollow in the lid to save space
- Ergonomically shaped handles with additional moulded recess on the side for flexible, convenient handling
- Dimensions, exterior (W x H x D): 442 x 151 x 357 mm; dimensions, interior (W x H x D): 375 x 107 x 311 mm
- Strong box made of impact- and shock-proof ABS plastic

Article No.	00 21 19 LB E
EAN	4003773081630
Net weight g	7800

technical change and errors excepted

L-BOXX® is a registered trademark of Sortimo International GmbH

Content 00 21 19 LB E (21)

Article No.			Quantity	Nominal size	
00 11 01	Knipex	KNIPEX TwinKey®, for all standard cabinets and shut-off systems	1		
08 26 145	Knipex	Needle-Nose Combination Pliers	1		
12 42 195	Knipex	KNIPEX MultiStrip 10, Automatic Insulation Stripper	1		
13 86 200	Knipex	Pliers for Electrical Installation	1		
16 95 01 SB	Knipex	KNIPEX ErgoStrip®, Universal Stripping Tool	1		
26 26 200	Knipex	Snipe Nose Side Cutting Pliers, (Stork Beak Pliers)	1	200 mm	
70 06 160	Knipex	Diagonal Cutter	1	160 mm	
74 06 200	Knipex	High Leverage Diagonal Cutter	1	200 mm	
86 03 180	Knipex	Pliers Wrench, pliers and a wrench in a single tool	1	180 mm	
87 01 180	Knipex	KNIPEX Cobra®, Hightech Water Pump Pliers	1	180 mm	
97 53 04	Knipex	Self-Adjusting Crimping Pliers for End Sleeves (ferrules), with lateral access	1		
98 52	Knipex	Cable Knife	1	185 mm	
98 25 01 SL	Knipex	Screwdriver (Slim) for cross-recessed screws, Pozidriv®	1	PZ1	
98 20 35 SL	Knipex	Screwdriver (Slim) for slotted screws	1	3,5 x 100 mm	
05003484001	Wera	16-part set of VDE interchangeable blades, slim	1		
004018	Wera	8100 SA 8 Zyklus set of metal ratchets, 28 parts	1	1/4"	
003760	Wera	Joker open-end wrench	1	10 x 13 mm	
101-0300	Picard	Locksmith's hammer	1	300 g	
361 252 1	Rennsteig	Electrician's Chisel	1	250 x 10 mm	
16135	Stabila	Model 70 Electric spirit level	1	430 mm	
18115	Stabila	Pocket Electric mini spirit level	1	68 mm	