



Counter stays

11401

Product no. **71040101**
GTIN **4018754342174**
Model **11401/1**

Label. Counter stay

- Properties.**
- for internal puller 11400/1-9
 - screw the spindle of the counter stay into the internal puller
 - insert and spread the internal puller
 - pull out the workpiece

Benefits.

For use with the internal puller 11400.

Supports reliable and fast extraction of tight fitting ball bearings, bushings, oil seals etc. .

Powerful spindle with fine thread provides reliable performance, even for demanding tasks.

To use, place the counter stay onto the housing, screw the spindle into the internal puller and pull out the component.

Made from robust steel for a long service life, even with heavy use.

Product highlights.



PRODUCT IMAGE
IN PROGRESS

Reliable grip.

The combination of a robust spindle, fixed clamping nut and a strong toggle handle ensures a secure grip and precise, centred pulling.



PRODUCT IMAGE
IN PROGRESS

Adapted access geometry.


The self-centering puller arms automatically adjust to the shape of the part to be removed. This facilitates handling and ensures an even distribution of the pull-off force.

For increased safety.

Thoughtfully designed, die-forged and precisely machined, hardened and tempered on state-of-the-art machines - the STAHLWILLE puller range offers numerous products for a wide range of applications. For example, terminal pullers, pullers for ball joints, counter stays or ball joint extractors - always in premium quality.



Technical drawing.



Technical attributes.

External hex drive (mm)	27 mm
for thread	M10
for model	11400/1; /2; /3; /4; /4a; /5
Size	1

Logistics data.

Depth mm (IFS)	170
Width mm (IFS)	75
Height mm (IFS)	25
WEEE/ElektroG	nicht ear-pflichtig
Length (packaged, mm)	195
Width (packaged, mm)	120
Height (packaging, mm)	40
Volume (packaged, dm3)	0.936 dm3
Product no.	71040101
Weight (gross, kg)	0,758

Weight PAP (kg)	0,006
Weight PVC (kg)	0,000
GTIN	4018754342174
Country of origin AWR	GERMANY
Region of origin	Nordrhein-Westfalen
Customs tariff no.	82055980
Packing standard	1
Weight (g)	750 g

Variants.

Product no.	Model No. (ERP)	Description	GTIN
71040101	11401/1	Counter stay	4018754342174
71040102	11401/2	Counter stay	4018754342181
71040103	11401/3	Counter stay	4018754342198

GTIN.



Images.





STAHLWILLE Eduard Wille GmbH

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH, Wuppertal