



1705

Air

Long Case

The Peli™ 1705 Air Case is a compact long case designed for AR pistols, Personal Defense Weapons, takedown shotguns, or fly-fishing rods and reels. Waterproof, dustproof and durable, the 1705 Air case is the solution to protect your gear. Peli Air cases are the toughest and lightest cases Peli has to offer. Each Peli Air case is up to 40 percent lighter than an average polymer case yet still extremely durable. The 1705 Air Case will lighten the load while travelling with your valued possessions.

- Limited Lifetime Warranty (Where applicable by law)
- Waterproof, crushproof, dustproof
- IP67 & MIL-SPEC certified
- Super-light proprietary HPX²™ Polymer - up to 40% lighter
- Press and Pull™ Latches
- Automatic Pressure Equalization Valve - balances interior pressure, keeps water out
- Fold down overmolded handle
- Waterproof O-ring seal
- Stainless steel padlock protectors
- Made in the USA
- Business Card Holder



CONFIGURATIONS



1705
Standard



1705NF
No Foam



1705WF
With Foam

DIMENSIONS

Interior (L×W×D)	32.01 x 12.15" x 6.51 (81.3 x 30.9 x 16.5 cm)
Exterior (L×W×D)	32.27 x 14.56" x 7.30 (82 x 37 x 18.5 cm)
Lid Depth	2.00" (5.1 cm)
Bottom Depth	4.31" (10.9 cm)
Total Depth	6.31" (16 cm)
Int Volume	1.47 ft ³ (0.042 m ³)
Padlock Hole Diameter	5/16" (12.7 cm)

MATERIALS

Body	Proprietary Polypropylene Blend
Latch	ABS
O-Ring	EPDM
Pins	Stainless Steel

Foam	Polyurethane
Purge Body	ABS
Purge Vent	Hi-Flow Gore-Tex 3 Micron Hydrophobic Non-Woven
Handle	Polypropylene and Thermoplastic Rubber Side Handle

COLOURS

■ Black

■ OCP Tan

WEIGHT

Weight With Foam	10.55 lbs (4.79 kg)
Weight Empty	8.90 lbs (4.04 kg)
Buoyancy	94.50 lbs (42.86 kg)

TEMPERATURE

Minimum Temperature	0°F (-17.8 °C)
Maximum Temperature	140°F (60 °C)

ACCESSORIES



1705FS
4 pc. Replacement Foam Set



1472
Shoulder Strap

Peli

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999
info@peli.com • www.peli.com

Document created on 08-19-26