



 PRODUCT-DETAILS

2601/6 WGL-53

Switch Rocker/button, Two-way switch with Neon lamp grey / blue-green - ocean



General Information

| | |
|-----------------------|---|
| Extended Product Type | 2601/6 WGL-53 |
| Product ID | 2CKA001085A1613 |
| EAN | 4011395992661 |
| Catalog Description | Switch Rocker/button, Two-way switch with Neon lamp grey / blue-green - ocean |
| Long Description | With neutral (transparent) lens. With illumination. |

Installation

| | |
|-----------------------------|---------------------|
| Instructions and Manuals | No document needed |
| Wiring Diagram | 2CKA000097E0045 |
| Mounting Type | Surface Mounted |
| Type of Fastening | Mounting with Screw |
| Mounting Orientation | Vertical |
| Modular Components Included | Complete Device |

Environmental

| | |
|----------------------|------|
| Degree of Protection | IP44 |
|----------------------|------|

Technical

| | |
|-----------------------------------|--|
| Data Sheet, Technical Information | No document needed |
| Function | Function lighting: Control and orientation |
| Number of Rocker Switches | 1 |
| Wiring Configuration | Two-way switch |
| Actuator Type | Rocker/button |
| Lamp Type | Neon lamp |
| Illumination | Optional |
| Lamp Color | White |
| Terminal Type | Screwless Terminals |

Electrical

| | |
|-------------------------|-------------------|
| Rated Voltage (U_r) | 250 V |
| Rated Current (I_n) | 10 A |
| Power Watt | LEDi / CFLi 100 W |

Design

| | |
|----------------------|---------------------------|
| Design Range | ocean |
| Surface Finishing | Untreated Matt |
| Material | Thermoplastic |
| Label Space Provided | With Optional Label Space |
| Label Space Size | 57.8 x 9.8 mm |
| RAL Number | Similar to RAL 7035 |
| Color | grey / blue-green |

Dimensions

| | |
|----------------------------|-------|
| Product Net Width | 74 mm |
| Product Net Height | 83 mm |
| Product Net Depth / Length | 55 mm |
| Product Net Weight | 124 g |

Engineering

| | |
|-------------------------------------|-----------------|
| Building Information Modeling – BIM | 9AKK108466A8423 |
|-------------------------------------|-----------------|

Material Compliance

| | |
|------------------|--|
| RoHS Declaration | 2CKA200000E0301 |
| RoHS Information | Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019 |

| | |
|---|--|
| REACH Declaration | 2CKA309999E9999 |
| REACH Information | True - contains substances > 0.1 mass percentage |
| REACH Date | 20250901 |
| Conflict Minerals Reporting Template (CMRT) | 9AKK108468A3363 |
| SCIP | a61b1624-9949-4c53-9475-730eb8a4ae86 Germany |
| Simplified SCIP | a61b1624-9949-4c53-9475-730eb8a4ae86 Germany |
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |
| WEEE B2C / B2B | Business To Consumer |

Certificates and Declarations

| | |
|--|-----------------|
| Declaration of Conformity - CE | 2CKA100000E0203 |
| EU Data Act Applicability and Compliance | Not Applicable |

External Classifications and Standards

| | |
|---------|--------------------------------|
| ETIM 9 | EC001590 - Installation switch |
| ETIM 10 | EC001590 - Installation switch |
| eClass | V11.0 : 27144053 |

Accessories

| Identifier | Description | Type | Quantity | Unit Of Measure |
|-----------------|--|--------------|----------|-----------------|
| 2CKA001761A1487 | Cable Entry blue green - ocean | 2134 W-53 | 1 | piece |
| 2CKA001761A1490 | Cable bushing blue green - ocean | 2138 W-53 | 1 | piece |
| 2CKA001761A1492 | Cable Entry blue green - ocean | 2086 W-53 | 1 | piece |
| 2CKA001799A0882 | Label Holder transparent - ocean | 1763-53 | 1 | piece |
| 2CKA001784A0777 | Illumination set Label holder LED 1 mA, 230 V clear transparent - ocean | 2152 NLI-53 | 1 | piece |
| 2CKA001716A0042 | Mounting Plate 1-gang brass | 2609 WS | 1 | piece |
| 2CKA001761A1489 | Cable Entry blue green - ocean | 2136 W-53 | 1 | piece |
| 2CKA001714A0286 | Symbol with Symbol "key" clear transparent | 2622 TR-101 | 1 | piece |
| 2CKA001714A0278 | Symbol with Symbol "bell" clear transparent | 2622 KI-101 | 1 | piece |
| 2CKA001714A0260 | Symbol with Symbol "light" clear transparent | 2622 LI-101 | 1 | piece |
| 2CKA001714A0252 | Symbol clear transparent | 2622 N-101 | 1 | piece |
| 2CKA001784A0719 | Illumination set for Switch/push button White Incandescent lamp, 40 mA, 24 V AC/DC | 8358 | 1 | piece |
| 2CKA001784A0321 | Illumination set for Switch/push button Orange Neon lamp, 1 mA, 230 V | 8346-1 | 1 | piece |
| 2CKA001784A0529 | Illumination set for Switch/push button White Incandescent lamp, 40 mA, 12 V | 8335-1 | 1 | piece |
| 2CKA001784A0024 | Illumination set for Switch/push button White Incandescent lamp, 40 mA, 3 ... 8 V | 8333-1 | 1 | piece |
| 2CKA001784A0016 | Illumination set for Switch/push button Orange Neon lamp, 0.6 mA, 230 V | 8332-1 | 1 | piece |
| 2CKA001714A0294 | Symbol red | 2622-12-101 | 1 | piece |
| 2CKA001761A1503 | Cable Entry blue green - ocean | 2137/10 W-53 | 1 | piece |
| 2CKA001761A1506 | Cable Entry blue green - ocean | 2137/11 W-53 | 1 | piece |

Categories

Low Voltage Products and Systems → Wiring Accessories - Light Switch Ranges → Surface Mounted Range → Mechanical Controls

