

RNF-100-3/16-X-SP

✓ ACTIVE

RAYCHEM | RAYCHEM RNF-100

TE Internal #: 5070054026

Heat Shrink Tubing, Clear, 2:1, Single Wall Tubing, Shrinks To 2.4 mm [.093 in], Irradiated Modified Polyolefin, RAYCHEM RNF-100

[View on TE.com >](#)



Heat Shrink Tubing > RNF-100-3 Heat Shrink Tubing



Tubing Product Type: **Heat Shrink Tubing**

Primary Product Color: **Clear**

Shrink Ratio: **2:1**

Wall Type: **Single Wall**

Recovered Inside Diameter (Max): **2.4 mm [.093 in]**

[All RNF-100-3 Heat Shrink Tubing \(99\)](#)

Features

Product Type Features

Tubing Product Type	Heat Shrink Tubing
Wall Type	Single Wall

Electrical Characteristics

Operating Voltage (Max)	.6 kV
-------------------------	-------

Body Features

Fluid Type	Gasoline, Hydraulic Fluid, Lubricating Oil, Water
Primary Product Color	Clear
Shrink Ratio	2:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Flexible

Dimensions

Recovered Wall Thickness (Nominal)	.5 mm[.02 in]
Recovered Wall Thickness (Tolerance)	.2 mm[.008 in]
Recovered Inside Diameter (Max)	2.4 mm[.093 in]
Expanded Inside Diameter (Min)	4.8 mm[.187 in]
Tubing Size Range	2.4 – 4.8 mm[.093 – .187 in]



Usage Conditions

Shrink Temperature (Min)	95 °C
Tubing Flammability Type	Non-Flame-Retardant
Operating Temperature Range	-55 – 135 °C
Recovery Temperature	121 °C

Operation/Application

Mechanical Resistance	Abrasion, Fluids, Mechanical Damage, Strain Relief
-----------------------	--

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Reel
------------------	------

Other

Meets Low Outgassing Requirements	No
Product Source	China, Czech Republic

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part

RNF-100-3/16-X-SP

Heat Shrink Tubing, Clear, 2:1, Single Wall Tubing, Shrinks To 2.4 mm [.093 in], Irradiated Modified Polyolefin, RAYCHEM RNF-100




numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | RAYCHEM RNF-100



Heat Shrink Tubing(839)



Orange Heat Shrink Tubing(44)



Power Cable Tubing & Accessories(5)



Single Wall Tubing(838)

Customers Also Bought



TE Part #5053104012
RNF-100-1/4-2-SP



TE Part #ZPF000000000205304
951-06 R 8-2 S 50 A5712



TE Part #YDIV43E11-35SNC009
RECP ASSY



TE Part #CAT-HST-RNF100-3
RNF-100-3 Heat Shrink Tubing



TE Part #ZPF000000000013515
DBAS 76G 27-0 SN 059



TE Part #148447-000
CWT-3-S

TE Part #950426-000
S1125-CS-34017

TE Part #ZPF000000000002616
402-0140-00

RNF-100-3/16-X-SP

Heat Shrink Tubing, Clear, 2:1, Single Wall Tubing, Shrinks To 2.4 mm [.093 in],
Irradiated Modified Polyolefin, RAYCHEM RNF-100



Documents

Product Drawings

RNF-100-3/16-X-SP

English

Datasheets & Catalog Pages

RNF-100 Pages from 9-1773447-9

English

Product Specifications

Application Specification

English