



ARIA 360™

NITRILE FOAM PALM WITH ECO FRIENDLY LINER AND TOUCH SCREEN CAPABILITIES

Lightweight nitrile foam glove with an outstanding durability and grip, eco friendly liner and touch screen capabilities.

FEATURES

- › Genium™ is an eco friendly liner with 1/3 of the ingredients by weight that are sustainably sourced and that requires 30% less energy to be produced.
- › Touchscreen capability on thumb and index finger
- › Anatomically designed with moisture wicking to deliver great comfort
- › Excellent grip in all conditions (dry wet, oily)
- › Low particle shedding for sensitive applications
- › Super soft liner
- › Patented nitrile foam palm coating enhances protection
- › Sanitized® antimicrobial finish provides extra freshness
- › Light thermal protection up to 100°C for a short period



SUITABLE FOR

Typical Industries

- Automotive
- Logistics
- Maintenance
- Manufacturing
- Utilities

Suitable Applications

- Assembly
- Goods Handling
- Light Fabrication
- Quality Inspection
- Warehousing

CERTIFICATION



EN 388:2016



4121A

EN407:2004



X1XXXX

See overleaf for explanation





ARIA 360™

PRODUCT INFORMATION

MATERIALS	LINER:	15 gauge Genium™, nylon, spandex
	COATING:	Foam nitrile
COLOUR	Grey / Black	
LENGTH (mm)	250 (size dependent)	
CUFF STYLE	Elasticated knit wrist	


RECOMMENDATIONS FOR USE

- **USE:** General handling glove. Not suitable for high thermal (beyond 100°C), electrical or chemical protection. Do not use near moving machines if there is a risk of entanglement
- **STORAGE:** Store in dry conditions in the original packaging and away from direct sunlight
- **CLEANING:** To clean, wipe with a damp cloth. Note: The performance characteristics of worn and laundered gloves may differ from the results shown. Inspect the gloves to ensure no damage is present.
- **LIFETIME:** Service life depends on the glove application and therefore cannot be specified. It is the responsibility of user to ensure the glove is suitable for its intended use


ORDERING DETAILS

SIZE	CODE	PACKAGING
6/XS	SKG00022FB	10 pairs per bag 120 pairs per case
7/S	SKG00022FD	
8/M	SKG00022FF	
9/L	SKG00022FH	
10/XL	SKG00022FJ	
11/XXL	SKG00022FL	

CERTIFICATION LEGENDS

MECHANICAL HAZARDS EN 388:2016
PERFORMANCE LEVELS*

*If tests are not performed or are not applicable, 'X' will be placed instead of a number/letter

HEAT AND FIRE
EN 407

EUROPE

www.globusgroup.com

E: sales@globus.co.uk
T: +44 (0)161 877 4747
F: +44 (0)161 877 4746

MIDDLE EAST AND AFRICA

www.globusgroup.com/gcc

E: gcc@globusgroup.com
T: +971 4 882 9962
F: +971 4 882 9963



Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM
 Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES

©2020 Globus (Shetland) Ltd | SKY-DATA-ARIA 360_1020_1