



- 01 4 SCREWS M3x5 TAPTITE POSI PAN ZINC PLATED INCLUDED WITH ENCLOSURE ASSY
- 02 DZUS Fastener  
Pilot 1/4 turn fastener range  
Part no's: 275-201-040 retainer  
285-102-161 receptacle  
290-718-191 stud assembly  
OR EQUIVALENT TO BE APPROVED BY TYCO
- 03 CABLE MANAGEMENT, CABLE GLANDS AND SPLICE HOLDERS PACKED IN PLASTIC BAG  
(SHOWN ON DRAWING IN SUGGESTED POSITION)
- 04 LASER LOGO AND LASER TEXT LABEL INCLUDED IN PLASTIC BAG

|                            |                                    |                                |                                |                   |   |                           |    |                             |                             |                      |                     |                             |             |                               |             |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|----------------------------|------------------------------------|--------------------------------|--------------------------------|-------------------|---|---------------------------|----|-----------------------------|-----------------------------|----------------------|---------------------|-----------------------------|-------------|-------------------------------|-------------|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|
| -                          | -                                  | -                              | -                              | -                 | 4 | -                         | 0  | -                           | -                           | -                    | -                   | -                           | 0-0504021-3 | 24                            | 4-1206480-4 |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| -                          | -                                  | -                              | -                              | -                 | 4 | -                         | 12 | -                           | -                           | -                    | -                   | -                           | 0-0504021-3 | 12                            | 2-1206480-4 |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| -                          | -                                  | -                              | -                              | -                 | 4 | -                         | 24 | -                           | -                           | -                    | -                   | -                           | -           | 0                             | 0-1206480-8 |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| (11) OFN SADDLE<br>QTY = 8 | (10) CABLE MAGM. SPIDER<br>QTY = 2 | (9) CABLE GLAND M25<br>QTY = 1 | (8) CABLE GLAND M20<br>QTY = 1 | (7) SPLICE HOLDER |   | (6) BLANKING PLUG ST-TYPE |    | (5) R.H. BRACKET<br>QTY = 1 | (4) L.H. BRACKET<br>QTY = 1 | (3) COVER<br>QTY = 1 | (2) TRAY<br>QTY = 1 | (1) COUPLING RECEPTACLE KIT |             | PART NUMBER                   | QTY         |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|                            |                                    |                                |                                | PART NUMBER       |   | PART NUMBER               |    |                             |                             |                      |                     | PART NUMBER                 |             |                               |             |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| CUSTOMER DRAWING           |                                    |                                |                                |                   |   |                           |    |                             |                             |                      |                     |                             |             |                               |             |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| AMP drawing N° : 1206480   |                                    |                                |                                |                   |   |                           |    |                             |                             |                      |                     |                             |             | MAT: MILD STEEL ZINTEC COATED |             |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |

|   |                      |  |  |  |  |
|---|----------------------|--|--|--|--|
| DRAWING STATUS  |                      | REVISION DESCRIPTION: - Design changes sliding tray.   |  |  |  |
| RELEASED  |                      | DRAWING BY<br>NAME: H. BLEUS<br>DATE: 28-FEB-03  | DRAWING REVISION BY<br>NAME: H. BLEUS<br>DATE: 05-MAY-04 | VOLUME OF MOULDED PART OR AREA OF UNFOLDED SHEETMETAL PART. Cm³ / Cm²<br>- |  |
|   |                      | DRAWING TITLE  |  |  |  |
| SCALE:<br>1000  | DRAWING FORMAT<br>A1 | F.O. 1U PANEL 24 ST-STYLE MM (220mm)   |  |  |  |
| ISO-SYMBOL<br>   | GENERAL TOLERANCE    |  |  |  |  |
|  <b>tyco</b> / <i>Electronics</i><br><small>Raychem N.V.</small><br>DIESTSESTEENWEG 69<br>B-3010 RESEL-LO, BELGIUM |                      | DRAWING SHEET REVISION NUMBER<br><b>D_0010589_01.AG</b>  |  | REVISION<br><b>AG</b>  |  |
|   |                      | THIS DRAWING AND INFORMATION SET FORTH HEREON ARE THE PROPERTY OF TYCO/Electronics/Raychem N.V. AND ARE TO BE HELD IN TRUST AND CONFIDENCE. PUBLICATION, DUPLICATION, DISCLOSURE OR USE FOR ANY PURPOSE NOT EXPRESSLY AUTHORIZED IN WRITING BY TYCO/Electronics IS PROHIBITED. |  |  |  |