

SK 3,8 REEL P5 WH CUS - Marker card



0825124

<https://www.phoenixcontact.com/in/products/0825124>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker card, can be ordered: by card, white, labeled according to customer specifications, mounting type: adhesive, for terminal block width: 5 mm

Your advantages

- Labeling service: Phoenix Contact can custom-label all SK ... markers in accordance with your requirements
- Ideal for labeling COMBICON connectors
- The SK labeling range offers self-adhesive marker strips for labeling products that do not have a marker groove

Commercial data

Item number	0825124
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BG8
Product key	BG8113
Catalog page	Page 102 (C-5-2013)
GTIN	4046356355070
Weight per piece (including packing)	0.89 g
Weight per piece (excluding packing)	0.89 g
Customs tariff number	49119900
Country of origin	PL

SK 3,8 REEL P5 WH CUS - Marker card



0825124

<https://www.phoenixcontact.com/in/products/0825124>

Technical data

Product properties

Product type	Labeled terminal marker
Pitch	5 mm
Type	Label

Marking

Number of marker strips	12
-------------------------	----

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

Foil strength	53 µm
Adhesive strength	20 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Ambient temperature (assembly)	> 15 °C
Recommended storage conditions	23 °C / 50% relative humidity. Storage in the original packaging is recommended prior to processing.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

Dimensions

Height	3.8 mm
Pitch	5 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

SK 3,8 REEL P5 WH CUS - Marker card

0825124

<https://www.phoenixcontact.com/in/products/0825124>




Notes

Order information:

Marking up to max. 25-pos.

Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

SK 3,8 REEL P5 WH CUS - Marker card



0825124

<https://www.phoenixcontact.com/in/products/0825124>

Classifications

ECLASS

ECLASS-13.0	27281101
-------------	----------

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

SK 3,8 REEL P5 WH CUS - Marker card



0825124

<https://www.phoenixcontact.com/in/products/0825124>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in