

Thick butyl-coated, chemical-resistant gloves, providing superior chemical protection

- **Specialized protection:** AlphaTec® 38-560 chemical-resistant gloves offer excellent protection against gas and ozone
- **Advanced ergonomics:** Featuring a natural, curved ergonomic shape and soft feel, these safety gloves ensure excellent flexibility and dexterity
- **Enhanced grip:** AlphaTec® 38-560 chemical-resistant gloves have a textured and rough finish for the safer handling of solvents and stronger acids
- **Added protection:** These protective gloves offer a beaded and longer, gauntlet-style cuff, ensuring easy donning and doffing as well as optimal tear resistance and safety



Industries

- Life Sciences
- Chemical
- Oil and gas

Applications

- Chemical Handling
- Charging and blending raw materials
- Equipment repair & maintenance
- Opening and draining pumps valves or lines

Key Features

- **Unflocked butyl gloves:** Enhanced chemical resistance
- **Ergonomic shape:** All-day comfort assured
- **Rough-textured gloves:** Optimized grip for safer handling

Vulcanization Chemical Accelerators

- 2-Mercaptobenzothiazole disulfide
- Dipentamethylenethiuramtetrasulphide
- Tetramethylthiuram disulfide

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards



0493

EN388: 2016



1010X

EN ISO 374-1:2016



ABIKPT

EN ISO 374-5:2016



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGT H	COLOR	PACKAGE
AlphaTec® 38-560	Coating Material: Butyl Polymer	7, 8, 9, 10, 11	350 / 13.8	Black	1 pair per inner bag, 10 inner bags per master bag, 10 master bags per carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.