

4 Port USB to RS232 Serial DB9 Adapter Hub

Product ID: ICUSB2324



This 4 Port USB to RS232 Serial Hub lets you connect up to four RS232 serial devices to your Mac or PC laptop or desktop computer through a single USB port, as though the computer offered built-on DB9M serial connectors.

The RS232 Serial Hub is compactly designed to preserve valuable workspace, and is bus-powered to eliminate the need for an external power adapter.

A cost-effective solution that bridges the compatibility gap between modern USB-capable computers and legacy RS232 serial peripherals, this dependable USB/RS232 Serial Adapter hub is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect modems, digitizer tablets, mice, bar code scanners, GPS receivers, ISDN terminal adapters, mobile phones, scanners, UPSes and POS equipment to your system
- Connect and program LED and Digital signage boards with serial communication ports

Features

- Bus powered, no external power adapter required
- Easy Plug-and-Play installation
- Fully compliant with USB 1.1 specifications and compatible with USB 2.0
- Provides you with four additional RS232 serial ports

Hardware	Warranty	Lifetime
	Bus Type	USB 2.0
	Chipset ID	FTDI - FT232RL
	Industry Standards	RS232
		USB 1.1
	Interface	Serial
	Port Style	External Hub
	Ports	4
Performance	FIFO	256 Bytes
	Max Baud Rate	921.6 Kbps
	Serial Protocol	RS-232
Connector(s)	Connector Type(s)	1 - USB Type-A (4 pin) USB 2.0 Male
	External Ports	4 - DB-9 (9 pin, D-Sub) Male
Software	OS Compatibility	Windows® CE (4.2, 5.0, 6.0), XP Embedded, 98SE, 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server® 2003, 2008 R2, 2012, 2012 R2, 2016 Mac OS® 10.6 to 10.14 Linux 2.4.x to 4.11.x <i>LTS Versions only</i>
Special Notes / Requirements	System and Cable Requirements	One free USB port
Power	Power Consumption (In Watts)	1 ~ 1.5W
Environmental	Humidity	5~95% RH
	Operating Temperature	0°C to 55°C (32°F to 131°F)
	Storage Temperature	-20 to 85°C (-4 to 185°F)
Physical Characteristics	Cable Length	6 ft [1.8 m]
	Enclosure Type	Plastic
	Product Height	1 in [2.6 cm]
	Product Length	5.9 in [15 cm]
	Product Width	2.6 in [66.5 mm]
	Weight of Product	6.2 oz [175 g]
Packaging Information	Package Height	2.1 in [53 mm]
	Package Length	8.7 in [22 cm]

	Package Width	5.9 in [15 cm]
	Shipping (Package) Weight	13.3 oz [378 g]
What's in the Box	Included in Package	1 - 4 Port Serial Hub 1 - USB Cable 1 - Mounting Bracket 1 - Driver CD 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.