

SceneSwitch LED Lamps

LED Scene Switch 60W A60 E27 WW FR ND 1BC/4



Some situations call for cool light, others benefit from the ambiance of a warm cozy glow. With Philips SceneSwitch LED lamps, you can have different light settings from just one bulb, candle or spot. And you don't need a dimmer! Optimize your lighting for relaxing, hobbies, recreation or working. Simply at the flick of a switch. And that's your existing switch! No extra installation is required.

Product data

• General Information

Cap-Base	E27 [E27]
Bulb Shape	A60 [A 60mm]
Nominal Lifetime (Nom)	15000 h
Switching Cycle	100000X
B50L70	15000
Technical Type	8/5/2-60 W
Setting(s)	

• Light Technical

Color Code	827/825/822 [CCT of 2700K/2500K/2200K]
Luminous Flux Setting(s)	806/320/80 lm
Luminous Flux (Rated) Setting(s)	806/320/80 lm
Color Designation	Warm/Extra Warm/Very Warm
Correlated Color Temperature Setting(s)	2700/2500/2200 K
Luminous Efficacy (rated) (Nom)	100.75 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

• Operating and Electrical

Input Frequency	50 to 60 Hz
Power (Rated) Setting(s)	8/5/2 W
Lamp Current (Nom)	100 mA

Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm Up Time To 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.5
Voltage (Nom)	220-240 V

• Temperature

T-Case Maximum (Nom)	80 °C
----------------------	-------

• Controls and Dimming

Dimmable	No
----------	----

• Mechanical and Housing

Bulb Finish	Frosted
-------------	---------

• Approval and Application

Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Efficiency Label (EEL)	A+
Energy Consumption kWh/1000 h	8 kWh

• Product Data

Full product code	871869658884000
Order product name	LED Scene Switch 60W A60 E27 WW FR ND 1BC/4
EAN/UPC - Product	8718696588840


PHILIPS

SceneSwitch LED Lamps

Order code 929001236501
Numerator - Quantity Per Pack 1
Numerator - Packs per outer box 4

Material Nr. (12NC) 929001236501
Net Weight (Piece) 0.065 kg



Dimensional drawing



SS Bulb 9.5W-60W 150D 2700-2200K E27 ND

Product	D	C
LED Scene Switch 60W A60 E27 WW FR ND 1BC/4	61 mm	111 mm

General Uniform Lighting



© 2016 Philips Lighting Holding B.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2016, September 30
data subject to change