



# CorePro LEDcapsule LV

## CorePro LEDcapsuleLV 1.7-20W GY6.35 827

The CorePro LEDcapsule is a true alternative to the halogen capsule. It is particularly suitable for task lighting and decorative applications in homes, shops, hotels and restaurants. Compatible with existing fixtures with G4 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers huge energy savings and minimizes maintenance costs without any compromise on light quality.

### Product data

General Information	
Cap-Base	GY6.35 [ GY6.35]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	1.7-20W
Light Technical	
Color Code	827 [ CCT of 2700K]
Luminous Flux (Nom)	210 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	123.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Power (Nom)	1.7 W
Lamp Current (Nom)	250 mA


Wattage Equivalent	20 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.4
Voltage (Nom)	AC Electronic 12 V
Temperature	
T-Case Maximum (Nom)	56 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy Efficiency Label (EEL)	A++
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	2 kWh
Product Data	
Full product code	871869679767900
Order product name	CorePro LEDcapsuleLV 1.7-20W GY6.35 827

CorePro LEDcapsule LV

EAN/UPC - Product	8718696797679
Order code	929001844302
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12

Material Nr. (12NC)	929001844302
Net Weight (Piece)	0.012 kg


Dimensional drawing




Capsule 12V 2W-20W 200lm 2700K GY6.35 ND

Product	D	C
CorePro LEDcapsuleLV 1.7-20W GY6.35 827	15 mm	39 mm


Photometric data



LEDcapsule CorePro 1.7-20W GY6.35 Capsule 827 ND





LEDcapsule CorePro 1.7-20W GY6.35 Capsule 827 ND



LEDcapsule CorePro 1.7-20W GY6.35 Capsule 827 ND

CorePro LEDcapsule LV

Lifetime



LEDcapsule CorePro 1.7-20W GY6.35 Capsule 827 ND

LEDcapsule CorePro 1.7-20W GY6.35 Capsule 827 ND

