

DEWALT

XR

WITH
FLEXVOLT
ADVANTAGE



TAKE
ADVANTAGE
OF MORE POWER



UP TO 77% MORE POWER*

DCS573 - 18V XR 190MM CIRCULAR SAW WITH FLEXVOLT ADVANTAGE

The DCS573 delivers up to 77% more power when paired with a DCB546 XR FLEXVOLT 6Ah battery versus a DCB184 18V XR 5Ah battery. With a 67mm depth of cut, outstanding dust management features, tool-free depth adjustment and an electronic safety brake, this rugged circular saw can tackle tough applications such as rip and bevel cuts and hard timber cutting.

18V XR WITH
FLEXVOLT
ADVANTAGE


GUARANTEED TOUGH.®

18V XR 190MM CIRCULAR SAW WITH FLEXVOLT ADVANTAGE

FLEXVOLT ADVANTAGE TECHNOLOGY
TAKE ADVANTAGE OF MORE POWER

INTEGRATED RAFTER HOOK
Safe storage when working on site

ELECTRONIC BRAKE
Stops blade quickly for increased safety




BRUSHLESS MOTOR
For long runtime and tool life

LED WORK LIGHT
Illuminates the cut line for increased visibility

TOOL FREE ADJUSTMENTS
Quick adjustments for depth and bevel control



Up to 77% more power when used with an XR FLEXVOLT battery*



67mm maximum depth of cut at 90°

*Using DCB546 6Ah XR FLEXVOLT battery vs. DCB184 5Ah 18V XR battery.

SPECIFICATIONS

BLADE DIAMETER	190 mm
BLADE BORE	30 mm
MAX. CUTTING CAPACITY	67 mm @ 90° / 51 mm @ 45°
NO LOAD SPEED	5500 rpm
WEIGHT	3.7 kg

KIT OPTIONS

DCS573T1	1 X 6Ah Battery, TSTAK Kitbox
DCS573NT	Bare, TSTAK Kitbox
DCS573N	Bare Unit

DCS573T1 KIT INCLUDES

- (1) DCS578 190mm Circular Saw
- (1) DCB546 6Ah XR FLEXVOLT Battery
- (1) DCB116 XR 6A Charger
- (1) TSTAK VI Kitbox
- (1) 24T TCT Blade
- (1) Rip Fence & Airlock Dust Extraction Port

RELATED ACCESSORIES



Extreme Runtime
190mm x 30mm
24T CSB

DT99562-QZ



Copyright ©2020 DeWALT. The following are examples of trademarks for one or more DeWALT power tools and accessories: the yellow and black color scheme; the "D"-shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.

GUARANTEED TOUGH.®

www.DEWALT.com