

"PanelSeT SF/SM 19" swing rack - 1600x800 mm - 31 modules"

Local distributor code: 398252308

NSYRSW31

EAN Code: 3606480067235

Main

Range	PanelSeT	
Accessory / separate part category	Mounting accessory	
Product or component type	19" rack	
Application	Electronic application	
For enclosure nominal dimensions	- H: 1600 mm	
Rack type	Swing	
Mounting location	On structure of enclosure	
Range compatibility	PanelSeT PanelSeT SF PanelSeT PanelSeT SM	
Device composition	fixing elements 2 800 mm swing rack supports 1 hinged rack 1 side lid with handle	
Quantity per set	Set of 1	
Number of units 19"	31	

Complementary

Rack coverage	Complete	
Rack position	Off-centered	
Material	Steel	
Enclosure/cubicle description	Floor-standing enclosure	
Surface finish	Zinc coated	
Lock type	Handle with ball lock	
fixing mode	By fixing element	
Adjustment	Adjustable in depth every 25 mm	
Colour	Side plate: grey (RAL 7035)	
Permanent permissible load	3.75 kg per unit with a maximum of 150 kg	
Opening of the 19" racks	Reversible 120 °	
Height	1600 mm	
Width	800 mm	
Depth	1501 mm	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.000 cm
Package 1 Width	73.000 cm
Package 1 Length	150.100 cm
Package 1 Weight	23.000 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	10
Package 2 Height	92.000 cm
Package 2 Width	120.000 cm
Package 2 Length	210.000 cm
Package 2 Weight	260.000 kg

Logistical informations

Country of origin

Contractual warranty

Coverage	Core product
Warranty	18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	178
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	No	
Packaging without single use plastic	No	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
SCIP Number	52da316e-d4e1-4114-85c0-32a03b2934fd	
REACh Regulation	REACh Declaration	

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No