



Extreme Jigsaw Blades

Extreme Jigsaw Blades engineered to deliver superior surface finish and precision with long cutting life. Innovative new design delivers excellent results in a variety of materials:

- *Superior precision* - 50% stronger blade body withstands higher side loads reducing blade breakage and wandering
- *Superior finish* - side chip path gullet design removes debris quickly and efficiently, delivering superior material surface finish
- *Superior life* - reinforced tooth design puts more steel behind each tooth for greater precision and longer blade life.



Cat No.	Barcode	Length	Working Length	Pitch	Pack Quantity	Min. Order Quantity
DT2107XM	5011402379743	106.5	81.5	2.7	5	10
DT2108XM	5011402379774	106.5	81.5	2.7	5	10
DT2109XM	5011402379798	106.5	81.5	4.0	5	10
DT2111XM	5011402379811	130.0	100	4.0	5	10
DT2112XM	5011402379835	106.5	81.5	4.0	5	10
DT2113XM	5011402379859	106.5	81.5	4.0	5	10
DT2116XM	5011402379873	106.5	81.5	2.7	5	10
DT2117XM	5011402379897	81.5	56.5	2.2	5	10
DT2119XM	5011402379910	106.5	81.5	3.0	5	10
DT2125XM	5011402379934	106.5	81.5	2.7	20	10
DT2126XM	5011402379958	106.5	81.5	4.0	20	10
DT2127XM	5011402379972	106.5	81.5	4.0	20	10

Primary Application
Wood - fine finish
Wood - fine finish extra wide
Wood - fast clean cut
Wood - fast, clean cut, extra long
Wood - fast cutting
Wood - rip & crosscut, extra wide
Downcutter for worktops
Wood - scroller
Aluminium, plastic & fibreglass
Wood - fine finish
Wood - fast, clean cut
Wood - fast cut

Extreme Jigsaw Blades - Cobalt Steel

Cat No.	Barcode	Length	Working Length	Pitch	Pack Quantity	Min. Order Quantity
DT2132QZ	5011402379996	106.5	81.5	2.7	3	1
DT2133QZ	5011402380015	106.5	81.5	2.7	3	1
DT2134QZ	5011402380039	106.5	81.5	4.0	3	1
DT2137QZ	5011402380053	106.5	81.5	4.0	3	1
DT2138QZ	5011402380077	106.5	81.5	4.0	3	1
DT2141QZ	5011402380091	106.5	81.5	2.7	3	1
DT2144QZ	5011402380144	106.5	81.5	3.0	3	1
DT2150GB	5011402380138	86.5	56.5	1.2	3	1
DT2151QZ	5011402380152	130	100	1.2	3	1
DT2154GB	5011402380176	86.5	56.5	1.7	3	1
DT2155QZ	5011402380190	130	100	1.7	3	1
DT2156GB	5011402380213	86.5	56.5	0.7	3	1

Primary Application
Wood - fine finish
Wood - fine finish extra wide
Wood - fast clean cut
Wood - fast cutting
Wood - rip & crosscut, extra wide
Downcutter for worktops
Aluminium, plastic & fibreglass
Metal - Thin (< 5mm)
Metal - Thin (< 5mm) Extra long
Metal - Thick (5-9mm)
Metal - Thick (5-9mm) Extra long
Sheet Metal

* Denotes - available by special order only

Price List - Sawing

Jigsaw Blades

Cat No.	Barcode	Length	Working Length	Pitch	Pack Quantity	Min. Order Quantity	List Price ex. VAT	Primary Application
DT2001XM	5011402370504	100	75	1.65	5	1	Not U.K.	Wood - Extra Fine Finish
DT2002XM	5011402370528	100	75	2.70	5	1	Not U.K.	Wood - Fine Finish
DT2003XM	5011402370542	100	75	2.50	5	1	Not U.K.	Worktops & Laminates
DT2004XM	5011402370566	100	75	4.00	5	1	Not U.K.	Wood - Fast Rough Cutting
DT2005XM	5011402370580	132	105	3.30	5	1	Not U.K.	Wood - Fast Smooth Cutting
DT2006XM	5011402370603	76	50	2.50	5	1	Not U.K.	Wood Scrolling - Fine
DT2041XM	5011402370627	100	90	3.00	5	1	Not U.K.	Aluminium
DT2042XM	5011402370641	76	50	1.20	5	1	Not U.K.	Metal - Thin
DT2043XM	5011402370665	76	50	2.00	5	1	Not U.K.	Metal - Thick
DT2081XM	5011402370689	132	105	1.8/2.6	5	1	14.71	Metal & Wood Multi-purpose
DT2101XM	5011402370702	76	50	1.00	1	1	11.14	Stainless Steel, Mild Steel
DT2102XM	5011402370726	76	54	n/a	1	1	4.62	Ceramic Tiles
DT2103XM	5011402370740	100	70	1.00	1	1	11.35	Fibreglass & Reinforced
DT2201XM	5011402370784	152	120	n/a	5	1	13.24	Soft Materials



Reciprocating Saw Blades

Cat No.	Barcode	Length	Tool Speed	Pitch	Pack Quantity	Min. Order Quantity	List Price ex. VAT	Primary Application
DT2365QZ	5035048025123	152	High	3.6-5.1	5	1	16.83	Wood
DT2366QZ	5035048025130	228	High	3.6-5.1	5	1	23.46	Wood
DT2370QZ	5035048025147	152	High	1.8-2.5	5	1	15.10	Wood & Metal
DT2371QZ	5035048025154	225	High	1.8-2.5	5	1	17.24	Wood
DT2374QZ	5035048025161	152	High	1.8	5	1	15.10	Metal
DT2377QZ	5035048025178	152	Low	1.4	5	1	15.10	Metal
DT2380QZ	5035048025185	152	Low	1.1	5	1	15.10	Metal
DT2386QZ	5035048025192	Mixed	Various	Mixed	5	1	17.65	Corded Assortment

Cordless Reciprocating Saw Blades

Cat No.	Barcode	Length	Tool Speed	Pitch	Pack Quantity	Min. Order Quantity	List Price ex. VAT	Primary Application
DT2390QZ	5035048025208	152	High	3.6-5.1	5	1	17.24	Wood (Cordless)
DT2393QZ	5035048025215	152	High	2.5	5	1	15.10	Wood (Cordless)
DT2396QZ	5035048025222	152	Low	1.4	5	1	15.10	Wood (Cordless)
DT2398QZ	5035048025239	Mixed	Various	Mixed	3	1	8.98	Cordless Assortment