



Socket

45

Product no. **02010020**
GTIN **4018754002030**
Model **45 20**



Label. 3/8 " Socket Size 20mm L.34mm

Properties.

- bi-hex with AS-Drive profile
- 3/8" internal square drive
- HPQ® high performance steel, chrome-plated
- DIN 3124 / ISO 2725-1 / ASME B 107.5M / DIN EN 3709


Technologies and features.



High Performance Quality (HPQ®)

Our HPQ® tool is made of wear-resistant high-performance steel, yet is thin-walled and lightweight. It withstands high torques and is ideal for work in confined spaces such as turbines.

Technical drawing.



Technical attributes.

Drive profile	bi-hex AS-Drive
Square drive inner (inch)	3/8 "
d1	26,2 mm
d2	20 mm
d3	19 mm
DIN	DIN 3124 / ISO 2725-1, ASME B 107.5M, DIN EN 3709
Length mm (L)	34 mm
Size [mm]	20 mm
t1	15,5 mm
t2	20,7 mm

Logistics data.

Depth mm (IFS)	29
Width mm (IFS)	27
Height mm (IFS)	27
WEEE/ElektroG	nicht ear-pflichtig
Length (packaged, mm)	136
Width (packaged, mm)	28
Height (packaging, mm)	30
Volume (packaged, dm3)	0.11424 dm3
Product no.	02010020
Weight (gross, kg)	0,305
Weight PAP (kg)	0,000
Weight PVC (kg)	0,005
GTIN	4018754002030
Country of origin AWR	GERMANY
Region of origin	Nordrhein-Westfalen
Customs tariff no.	82042000
Packing standard	5
Weight (g)	51 g

Variants.

Product no.	Model No. (ERP)	Description	GTIN
02010007	45 7	3/8 " Socket Size 7mm L.24mm	4018754001903
02010008	45 8	3/8 " Socket Size 8mm L.25mm	4018754001910
02010009	45 9	3/8 " Socket Size 9mm L.25mm	4018754001927

02010010	45 10	3/8 " Socket Size 10mm L.27mm	4018754001934
02010011	45 11	3/8 " Socket Size 11mm L.27mm	4018754001941
02010012	45 12	3/8 " Socket Size 12mm L.28mm	4018754001958
02010013	45 13	3/8 " Socket Size 13mm L.30mm	4018754001965
02010014	45 14	3/8 " Socket Size 14mm L.30mm	4018754001972
02010015	45 15	3/8 " Socket Size 15mm L.31mm	4018754001989
02010016	45 16	3/8 " Socket Size 16mm L.31mm	4018754001996
02010017	45 17	3/8 " Socket Size 17mm L.31mm	4018754002009
02010018	45 18	3/8 " Socket Size 18mm L.32mm	4018754002016
02010019	45 19	3/8 " Socket Size 19mm L.32mm	4018754002023
02010020	45 20	3/8 " Socket Size 20mm L.34mm	4018754002030
02010021	45 21	3/8 " Socket Size 21mm L.34mm	4018754002047
02010022	45 22	3/8 " Socket Size 22mm L.35mm	4018754002054
02010024	45 24	3/8 " Socket Size 24mm L.35mm	4018754149148

GTIN.



STAHLWILLE Eduard Wille GmbH

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0

info@stahlwille.de · www.stahlwille.com

© STAHLWILLE Eduard Wille GmbH, Wuppertal