




**Part Number :** [2262451042](#)  
**Product Description :** Mini-Fit Versa Color-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 4.20mm Pitch, Dual Row, 150.00mm Length, 4 Circuits, Red  
**Series Number :** 226245  
**Status :** Active  
**Product Category :** Power and Signal Cable Assemblies



Documents & Resources

Drawings  
[2262451042\\_sd.pdf](#)

Product Environment Compliance

Compliance

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                          |
| China RoHS         |  |
| EU ELV             | Not Relevant                                                                          |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21                                                    |
| REACH SVHC         | Not Contained per D(2024)6225-DC (07 Nov 2024)                                        |
| EU RoHS            | Compliant per EU 2015/863                                                             |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

---

## Part Details

### General

|                        |                                                                                                                              |
|------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Status                 | Active                                                                                                                       |
| Category               | Power and Signal Cable Assemblies                                                                                            |
| Series                 | 226245                                                                                                                       |
| Description            | Mini-Fit Versa Color-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 4.20mm Pitch, Dual Row, 150.00mm Length, 4 Circuits, Red |
| Application            | Power, Wire-to-Board, Wire-to-Wire                                                                                           |
| Assembly Configuration | Single Ended Connector                                                                                                       |
| Connector to Connector | Mini-Fit Versa Color-to-Pigtail                                                                                              |
| Product Name           | Mini-Fit Versa Color                                                                                                         |
| Type                   | Discrete Wire Assembly                                                                                                       |
| UPC                    | 198282202745                                                                                                                 |

### Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 9.0A |
| Voltage - Maximum             | 600V |

### Physical

|                                |                |
|--------------------------------|----------------|
| Cable Length                   | 150.00mm       |
| Circuits (Loaded)              | 4              |
| Circuits (maximum)             | 4              |
| Color - Resin                  | Red            |
| Gender                         | Female-Pigtail |
| Lock to Mating Part            | Yes            |
| Material - Metal               | Brass          |
| Material - Plating Mating      | Tin            |
| Material - Plating Termination | Tin            |
| Material - Resin               | Nylon          |
| Net Weight                     | 4.215/g        |
| Number of Rows                 | 2              |
| Overmolded                     | No             |
| Packaging Type                 | Bag            |

|                             |                      |
|-----------------------------|----------------------|
| Pitch - Mating Interface    | 4.20mm               |
| Single Ended                | Yes                  |
| Termination Interface Style | Crimp or Compression |
| Wire/Cable Type             | UL 1007              |
| Wire Insulation Diameter    | 2.45mm               |
| Wire Size (AWG)             | 16                   |

---

## Mates With / Use With

### Mates with Part(s)

| Description                         | Part Number   |
|-------------------------------------|---------------|
| Mini-Fit Jr. Dual Row Plug Housings | <u>46993</u>  |
| Mini-Fit Vertical Dual Row Headers  | <u>172447</u> |