

# ▲ 2500 SERIES - 2530V



## P3V Disposable Cup-Shape Respirator

The 2500 SERIES disposable respirators with soft inner seal offer an outstanding level of protection and fit. Suitable for protection against a broad range of particulate hazards.

### KEY FEATURES

- ▶ Lightweight, cup shaped respirator
- ▶ Low profile exhalation valve to reduce heat and moisture build up
- ▶ Four point headstrap adjustment
- ▶ Preformed nosebridge with additional nose clip for a secure fit
- ▶ Features a full foam inner face seal for comfortable secure fit
- ▶ Conforms to EN 149:2001+A1:2009 FFP3 NR



### ORDERING INFORMATION

**Part Number:** 2530V

**Packaging:** 10 singles per box  
12 boxes per carton  
120 singles per carton

**Certification:** EN149:2001+A1:2009  
FFP3 NR

### SUITABLE APPLICATIONS

Protects from non-toxic dust and oil/water based particulates. Some suitable applications include:

- **Manufacture of Batteries (Ni-Cad)**
- **Construction**
- **Infection Control**
- **Metalworking**
- **Mining**
- **Pharmaceutical Industry**
- **Ship Building/Repair**
- **Underground Civil Engineering**
- **Disposal of Waste**
- **Woodworking Industry**

# A 2500 SERIES - 2530V



## P3V Disposable Cup-Shape Respirator

### TECHNICAL SPECIFICATIONS

#### MATERIALS

COMPONENT	MATERIAL
<b>Outer Cover:</b>	Polypropylene
<b>Inner Cover:</b>	Melt-Blown [Polypropylene]
<b>Filter Media:</b>	High Filtration Efficiency (Non-woven textile)
<b>Nosefoam</b>	Polyurethane
<b>Headstrap:</b>	Latex-Free Synthetic Rubber
<b>Valve Cover:</b>	Polypropylene

#### DIMENSIONS

ITEM	LENGTH (mm)	WIDTH (mm)	HEIGHT (mm)
<b>Respirator</b>	150	135	50

### CERTIFICATION

EU certification according to Regulation (EU) 2016/425 issued by: BSI Group The Netherlands B.V. Say Building, John M. Keynesplein 9, 1066 EP Amsterdam, Netherlands [N.B. No. 2797].

### RECOMMENDATIONS FOR USE

This respirator is disposable and recommended for single shift use only.

Do not attempt to clean or re-use.

[www.alphasolway.com](http://www.alphasolway.com) T: +44 (0)1461 202452 E: [alphasolway.sales@globusgroup.com](mailto:alphasolway.sales@globusgroup.com)

ALPHA SOLWAY LTD, Factory 1, Queensberry Street, Annan, DG12 5BL, UK

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary. © 2020 Alpha Solway Ltd

Part of  
**Globus**  
GROUP