



## Notice : *BOA MIXT P ¾*

Index : 2

### GUYARD SAS

22-24, rue Lucien Rouzet  
Z.A. Villedieu sur Indre/Niherne  
36250 NIHERNE FRANCE

### Medium risks - Category II PPE

EN 420 : 2003+ A1 : 2009 EN 388 : 2016  
EN ISO 13997 : 1999

### FEATURES:

- Polyamide knit glove, 3/4 polyurethane and nitril coating.
- Breathable aerated back and fingers.
- External palm surface with « dots ».
- Elastic wrist with coloured overlock to indicate size. Gauge15.
- Length 220 to 270 mm depending on size.

### AVAILABLE SIZES :

Size 6 to 10.

### PRECAUTIONS FOR USE :

- Wear the gloves on dry and clean hands. It is recommended to test the gloves first. Actual use conditions may be different from the EU type tests.
- Before reusing, check the gloves for defects, holes, tears, unusual wear, etc.
- Expiration date : 5 years from the date of manufacture stated on the glove.

### SAFETY COMFORT AND DEXTERITY :

- Dexterity level 5.
- The glove does not contain substances at levels which are known or suspected to have harmful effects on the hygiene or health of the user under the expected conditions of use.

### PACKAGING :

- In case of unpacking, a copy of the instruction sheet must be enclosed with the next smallest package.
- Bag of 10 pairs.
- Box of 100 pairs.

### MARKING :

The CE marking on this glove indicates compliance with the essential health and safety requirements of the European regulation 2016/425 on personal protective equipment (PPE).

EN 388 : 2016



4 1 2 1 X

### PERFORMANCE LEVEL :

EN 388 : 2016+A1 2018

- |                         |     |
|-------------------------|-----|
| • Abrasion :            | 4/4 |
| • Cutting :             | 1/5 |
| • Tearing :             | 2/4 |
| • Perforation :         | 1/4 |
| • Cutting (ISO 13997) : | X/F |

### PROTECTION LIMITS :

- Do not use for handling objects with a temperature above 50°C.
- Do not use for handling chemicals or liquids.

### RECOMMENDED USES :

- Handling of dry or very slightly oily parts.
- Delicate and precise applications, electronics assembly, work on microprocessors, automotive industry.

### CARE AND STORAGE :

No particular care is recommended. It is advised to store the products in a dark, cool, dry and ventilated area.

### RECOMMENDATION FOR END-OF-LIFE :

End-of-life destruction must be controlled and respect European traceability and environmental requirements.

EU Type Certificate issued according to Module B Regulation (EU) 2016/425  
The EU Declaration of Conformity is available on

CTC n° :0075  
[www.guyard-sa.com](http://www.guyard-sa.com)