



GREEN ULTRA LITE

EN ISO 21420 : 2020



EN 388



4 1 2 1 A

EN 407



X 1 X X X X



EN 388 : 2016 +A1 : 2018

- ABRASION : 4/4
- BLADE CUT : 1/5
- TEARING : 2/4
- PERFORATION : 1/4
- CUTTING BY SHARP OBJECT (ISO 13997) : A/F

EN 407 : 2020

- FIRE BEHAVIOR : X/4
- CONTACT HEAT : 1/4
- CONVECTIVE HEAT : X/4
- RADIANT HEAT : X/4
- SMALL SPLASHES OF LIQUID METAL : X/4
- LARGE SPLASHES OF LIQUID METAL : X/4

FEATURES

- GLOVE LINING RECYCLED POLYETHYLENE TEREPHTHALATE (PET) 40%, NYLON 35%, ELASTHANNE 15%, SPANDEX 10%, GAUGE 18
- NITRILE MICRO FOAM COVER
- COLOR PURPLE/BLACK

RECOMMENDED USES

- DIY WORK
- CAR ASSEMBLY, SMALL PARTS HANDLING
- LOGISTICS AND WAREHOUSING
- AIRPORT SECURITY AND BAGGAGE HANDLING

PRECAUTIONS FOR USE

- WEAR GLOVES ON CLEAN, DRY HANDS
- IT IS RECOMMENDED TO CARRY OUT A PRELIMINARY TEST UNDER ACTUAL CONDITIONS OF USE, WHICH MAY DIFFER FROM EU TYPE TESTING
- BEFORE RE-USE, CHECK GLOVES FOR DEFECTS, HOLES, TEARS, ABNORMAL WEAR, ETC

AVAILABLE SIZES



CE MARKING

- THIS MARKING SIGNIFIES COMPLIANCE WITH THE ESSENTIAL REQUIREMENTS PROVIDED FOR BY EUROPEAN REGULATION 2016/425, RELATING TO PERSONAL PROTECTIVE EQUIPMENT

SAFETY, COMFORT, AND DEXTERITY

- DEXTERITY: LEVEL 5
- THIS GLOVE DOES NOT CONTAIN ANY SUBSTANCES AT LEVELS WHICH ARE KNOWN OR SUSPECTED TO HAVE ADVERSE EFFECTS ON THE HYGIENE OR HEALTH OF THE USER UNDER THE EXPECTED CONDITIONS OF USE

STORAGE AND MAINTENANCE

- STORE PRODUCTS IN A DRY, COOL, WELL-VENTILATED PLACE, AWAY FROM LIGHT, SUNLIGHT AND ULTRAVIOLET RAYS, LEAVING THEM IN THEIR ORIGINAL PACKAGING
- WHEN CORRECTLY STORED, GLOVES RETAIN THEIR PROPERTIES WITHOUT UNDERGOING MAJOR CHANGES
- NO SPECIAL MAINTENANCE IS RECOMMENDED
- NON-WASHABLE



DISPOSAL

- END-OF-LIFE DESTRUCTION MUST BE CONTROLLED AND COMPLY WITH EUROPEAN TRACEABILITY AND ENVIRONMENTAL REQUIREMENTS

PACKAGING

- IN CASE OF DECONDITIONING, A COPY OF THE NOTICE MUST BE ENCLOSED WITH THE SMALLEST PACKAGING
- BAG OF 10 PAIRS
- BOX OF 100 PAIRS

LIMITATIONS OF PROTECTION

- DO NOT USE FOR HANDLING OBJECTS OVER 100°C
- DO NOT USE FOR HANDLING CHEMICALS OR LIQUIDS

EU TYPE CERTIFICATE ISSUED IN ACCORDANCE WITH MODULE B REGULATION (EU) 2016/425 - SATRA N°2777

THE EU DECLARATION OF CONFORMITY IS AVAILABLE ON REQUEST. CONTACT US VIA OUR WEBSITE WWW.GUYARD-SA.COM, "CONTACT" SECTION