

# GPA 610X610X1,5... - Engraving plate for outdoor use



0811435

<https://www.phoenixcontact.com/gb/products/0811435>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Engraving plate for outdoor use, material thickness: 1.5 mm, length: 610 mm, width: 610 mm, engraving plate

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 0811435                        |
| Packing unit                         | 10 pc                          |
| Minimum order quantity               | 10 pc                          |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BG2415                         |
| Product key                          | BG2415                         |
| GTIN                                 | 4017918906481                  |
| Weight per piece (including packing) | 158.75 g                       |
| Weight per piece (excluding packing) | 158.75 g                       |
| Customs tariff number                | 39205100                       |
| Country of origin                    | DE                             |

# GPA 610X610X1,5... - Engraving plate for outdoor use



0811435

<https://www.phoenixcontact.com/gb/products/0811435>

## Technical data

### Product properties

|              |                |
|--------------|----------------|
| Product type | Device marking |
|--------------|----------------|

### Marking

|                             |   |
|-----------------------------|---|
| Number of individual labels | 1 |
|-----------------------------|---|

### Mounting

|               |              |
|---------------|--------------|
| Mounting type | screw, rivet |
|---------------|--------------|

### Material specifications

|          |        |
|----------|--------|
| Color    | silver |
| Material | ABS    |

### Environmental and real-life conditions

#### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
|---------------|--------------------------------|

#### Wipe resistance of inscriptions

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 |
|---------------|-------------------------------------|

#### Ambient conditions

|                                                     |                                                                                 |
|-----------------------------------------------------|---------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | -20 °C ... 85 °C                                                                |
| Recommended ambient temperature (storage/transport) | 23 °C                                                                           |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

### Dimensions

|                   |         |
|-------------------|---------|
| Width             | 610 mm  |
| Height            | 1.5 mm  |
| Length            | 610 mm  |
| Material strength | 1.50 mm |

#### Text field

|                   |        |
|-------------------|--------|
| Text field width  | 610 mm |
| Text field height | 610 mm |

# GPA 610X610X1,5... - Engraving plate for outdoor use



0811435

<https://www.phoenixcontact.com/gb/products/0811435>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001288 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# GPA 610X610X1,5... - Engraving plate for outdoor use



0811435

<https://www.phoenixcontact.com/gb/products/0811435>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)