

# Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

**Supplier's name or trade mark:** Radium

**Supplier's address:** Radium Customer Service, Dr. Eugen Kersting Str. 6, 51688 Wipperfürth, DE

**Model identifier:** 4008597177330

## Type of light source:

Lighting technology used:	MH	Non-directional or directional:	NDLS
Light source cap-type (or other electric interface)	E40		
Mains or non-mains:	NMLS	Connected light source (CLS):	No
Colour-tuneable light source:	No	Envelope:	Second + Non-clear
High luminance light source:	No		
Anti-glare shield:	No	Dimmable:	No

## Product parameters

Parameter	Value	Parameter	Value
-----------	-------	-----------	-------


### General product parameters:

Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer	450	Energy efficiency class	F
Useful luminous flux ( $\phi_{use}$ ), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)	41 100 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	3 400
On-mode power ( $P_{on}$ ), expressed in W	444,0	Standby power ( $P_{sb}$ ), expressed in W and rounded to the second decimal	0,00
Networked standby power ( $P_{net}$ ) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set	64
Outer dimensions without separate control gear, lighting control	Height	120	Spectral power distribution in the range 250 nm to 800 nm, at full-load
	Width	290	
	Depth	120	
			See image in last page

parts and non-lighting control parts, if any (millimetre)			
Claim of equivalent power <sup>(a)</sup>	-	If yes, equivalent power (W)	-
		Chromaticity coordinates (x and y)	0,414 0,399

(a): not applicable;

(b): not applicable;



Model placed on the Union market from 01/10/2021.



**EPREL registration number:** 566108

<https://eprel.ec.europa.eu/qr/566108>

**Supplier:** Radium Lampenwerk GmbH (Manufacturer)

**Website:** [www.radium.de](http://www.radium.de)

**Customer care service:**

**Name:** Radium Customer Service

**Website:** [www.radium.de](http://www.radium.de)

**Email:** [customerservice@radium.de](mailto:customerservice@radium.de)

**Phone:** +49 2267 81 1

**Address:**

Dr. Eugen Kersting Str. 6  
51688 Wipperfürth  
Germany