

FBSK 5-7,5 - Plug-in bridge

1928372

<https://www.phoenixcontact.com/gb/products/1928372>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bridge, fully insulated, pitch 7.5 mm, 5-pos.

Commercial data

Item number	1928372
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AARZFD
Product key	AARZFD
Catalog page	Page 830 (C-1-2013)
GTIN	4017918606602
Weight per piece (including packing)	5.09 g
Weight per piece (excluding packing)	5.02 g
Customs tariff number	85389099
Country of origin	PL

FBSK 5-7,5 - Plug-in bridge

1928372

<https://www.phoenixcontact.com/gb/products/1928372>



Technical data

Product properties

Product type	Bridge
Product family	FBSK
Product line	COMBICON Terminals Special
Number of positions	5
Pitch	7.5 mm
Number of connections	5
Number of rows	1
Number of potentials	5

Dimensions

Pitch	7.5 mm
-------	--------

Material specifications

Material data - contact

Note	WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201
Contact material	Cu alloy

Material data - housing

Color (Housing)	red (3001)
Insulating material	PA
Insulating material group	I
CTI according to IEC 60112	600
Flammability rating according to UL 94	V0
Glow wire flammability index GWFI according to EN 60695-2-12	850
Glow wire ignition temperature GWIT according to EN 60695-2-13	775
Temperature for the ball pressure test according to EN 60695-10-2	125 °C

Connector

Connection 1

Insulating material	PA
CTI according to IEC 60112	600

FBSK 5-7,5 - Plug-in bridge

1928372

<https://www.phoenixcontact.com/gb/products/1928372>



Classifications

ECLASS

ECLASS-13.0	27460406
-------------	----------

ETIM

ETIM 9.0	EC002943
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FBSK 5-7,5 - Plug-in bridge

1928372

<https://www.phoenixcontact.com/gb/products/1928372>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	0.06 kg CO2e
---------	--------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk