


SES code marker cards
E 14 Miniature
Black print on white background



SES® - MARKERS
Grade TEV





Cards with self-adhesive marking strips E 14 Miniature (Grade TEV)
Card dimensions : 255 x 30 mm - Figure and letter height : 1,8 mm

Strips per card :	60 to 104 strips*	Adhesion :	2,5 N/cm
Strip width :	4,5 to 9 mm*	Tensile strength :	80 N/cm
Strip length :	14 mm	Temperature range :	-30°C to + 105°C (class A)
	(for wires Ø < 4 mm)		-40°C to+ 150°C (short duration)
Material :	TEV (vinyl covered cotton)	Operating temperatures :	+10°C to + 40°C
Strip thickness :	0,30 mm	Pack :	10 cards or 1 card
	*according to legends		

Cards with figures in series Type E 14 B Miniature white background
figures in series

Standard cards are only available in white with black print.

legend	article number	strips number	dimensions
	2 strips per legend		
0 - 49	0301 0009 001 S49	100	4,5 x 14 mm
50 - 99.	0301 0009 001 S99	100	4,5 x 14 mm
100 - 136	0301 0009 001 S136	74	6 x 14 mm
137 - 173	0301 0009 001 S173	74	6 x 14 mm
174 - 210	0301 0009 001 S210	74	6 x 14 mm
211 - 247	0301 0009 001 S247	74	6 x 14 mm
248 - 284	0301 0009 001 S284	74	6 x 14 mm
285 - 321	0301 0009 001 S321	74	6 x 14 mm
322 - 358	0301 0009 001 S358	74	6 x 14 mm
359 - 395	0301 0009 001 S395	74	6 x 14 mm
396 - 432	0301 0009 001 S432	74	6 x 14 mm
433 - 469	0301 0009 001 S469	74	6 x 14 mm
470 - 506	0301 0009 001 S506	74	6 x 14 mm
507 - 543	0301 0009 001 S543	74	6 x 14 mm
544 - 580	0301 0009 001 S580	74	6 x 14 mm
581 - 617	0301 0009 001 S617	74	6 x 14 mm
618 - 654	0301 0009 001 S654	74	6 x 14 mm
655 - 691	0301 0009 001 S691	74	6 x 14 mm
692 - 728	0301 0009 001 S728	74	6 x 14 mm
729 - 765	0301 0009 001 S765	74	6 x 14 mm



Standard pack: 10 cards same legend.





Cards with self-adhesive marking strips E 14 Miniature (Grade TEV)
Card dimensions : 255 x 30 mm - Figure and letter height : 1,8 mm

Cards with letters or figures in series Type E 14 B Miniature white background

Cards with letters or figures in series

Standard cards are only available in white with black print.

legend	article number	strips number	dimensions	legend	article number	strips number	dimensions
	2 strips per legend				4 strips per legend		
766 - 802	0301 0009 001 5802	74	6 x 14 mm	A - Z	0301 0009 001 A-Z	104	4,5 x 14 mm
803 - 839	0301 0009 001 5839	74	6 x 14 mm	a - z	0301 0009 001 MA-Z	104	4,5 x 14 mm
840 - 876	0301 0009 001 5876	74	6 x 14 mm				
877 - 913	0301 0009 001 5913	74	6 x 14 mm				
914 - 950	0301 0009 001 5950	74	6 x 14 mm				
951 - 987	0301 0009 001 5987	74	6 x 14 mm				
988 - 1019	0301 0009 001 1019	64	7,5 x 14 mm				

Standard pack: 10 cards same legend.



SES code marker cards
E 14 Miniature
Black print on white background





SES® - MARKERS
GradeTEV

Cards with repeated figures Type E 14 B Miniature white background

Standard cards are only available in white with black print.

Repeated upper and lower case letters and other legends

Legend	article number	number	strips	dimensions
A	0301 0009 001 A	100		4,5 x 14 mm
B	0301 0009 001 B	100		4,5 x 14 mm
C	0301 0009 001 C	100		4,5 x 14 mm
D	0301 0009 001 D	100		4,5 x 14 mm
E	0301 0009 001 E	100		4,5 x 14 mm
F	0301 0009 001 F	100		4,5 x 14 mm
G	0301 0009 001 G	100		4,5 x 14 mm
H	0301 0009 001 H	100		4,5 x 14 mm
I	0301 0009 001 I	100		4,5 x 14 mm
J	0301 0009 001 J	100		4,5 x 14 mm
K	0301 0009 001 K	100		4,5 x 14 mm
L	0301 0009 001 L	100		4,5 x 14 mm
M	0301 0009 001 M	100		4,5 x 14 mm
N	0301 0009 001 N	100		4,5 x 14 mm
O	0301 0009 001 O	100		4,5 x 14 mm
P	0301 0009 001 P	100		4,5 x 14 mm
Q	0301 0009 001 Q	100		4,5 x 14 mm
R	0301 0009 001 R	100		4,5 x 14 mm
S	0301 0009 001 S	100		4,5 x 14 mm
T	0301 0009 001 T	100		4,5 x 14 mm
U	0301 0009 001 U	100		4,5 x 14 mm
V	0301 0009 001 V	100		4,5 x 14 mm
W	0301 0009 001 W	100		4,5 x 14 mm
X	0301 0009 001 X	100		4,5 x 14 mm
Y	0301 0009 001 Y	100		4,5 x 14 mm
Z	0301 0009 001 Z	100		4,5 x 14 mm



+	0301 0009 001+	100	4,5 x 14 mm
-	0301 0009 001 -	100	4,5 x 14 mm

Standard pack: 10 cards same legend.

