



PRODUCT NUMBER: 21-1518B
Honeywell CoreShield™
Gloves - 21-1518B

CoreShield, 18 gauge nylon black liner, nitrile micro-foam black coating, A1/A



Overview

Reference Number

21-1518B

Product Type

Gloves

Line

Cut resistant

Brand

Honeywell

Industry

- Automotive and Part Manufacturer
- Building and Construction
- Glass Industries
- Logistics
- Metal steel

Features & Benefits

Feature

CoreShield™ Engineered Yarn

Benefit

One of the lightest cut-protective gloves in the market, help to prevent hand fatigue for workers who need to wear them all day long. Skin-friendly yarns that reduce allergy and provide excellent dexterity

Feature

CoreShield™ High Performance Micro-Foam Nitrile coating

Benefit

Provides 360° breathability, excellent grip performance, abrasion resistance for x2 durability, reduced hand fatigue and excellent dexterity.

Feature

Color-coded marking system

Benefit

For easy gloves selection you need for your application

Feature

Thumb reinforcement

Benefit

For greater wear resistance and extended product life

Feature

Washable

Benefit

Reduced cost of ownership

Feature

Hand and wrist protection

Benefit

A longer cuff ensures wrist protection

Feature

Touchscreen resistive and capacitive

Benefit

To operate touch panels of industrial machines and smartphone touchscreens without taking their gloves off

Feature

Gauge 18

Benefit

For an extraordinary fit/dexterity

Technical Description

Description

CoreShield, 18 gauge nylon black liner, nitrile micro-foam black coating, A1/A

Product Technology

CoreShield Engineered yarn and high performance micro-foam Nitrile coating

Fiber

Nylon

Gauge

18

Glove/liner color

Black

Coating Type

Nitrile micro-foam

Coating Color

Black

Length

255mm size 9

Sizes

6XS - 11XXL

EN 388 - Mechanical Hazards Abrasion Resistance

Abrasion resistance	4
Cutting resistance (Coupe test)	X
Tear resistance	2
Puncture resistance	1
Cutting resistance (TDM test)	A

ASTM D3389-05

ANSI Level Abrasion Resistance	6
--------------------------------	---

ASTM F1790-97

ANSI Level Cut Resistance

A1

Packaging Label

UOM

Pairs

Literature & Documents

CoreShield Micro foam Data Sheet UK

http://www.honeywellsafety.com/supplementary/documents_and_downloads/secured/gloves/4295003580/1033.aspx

Packaging

Unit of Measure

PAA

Quantity per Box/Pack/Case

10

Quantity per Carton

100

Quantity for Minimum Order

100

Country of Origin

China