



Hand protection

EOS NOCUT VV909

LONG-LASTING CUT WORK

Impact glove for heavy work, with high flexibility and lightness thanks to its PVC reinforcements made like honeycomb



Specific benefits



Hygiene

- Nitrile means no risk of allergies for users



Performance

- Flexible reinforcements for added protection against impact and pinching
- The nitrile coating gives people working in oily/greasy environments an excellent grip on the objects they handle

Applications

- Public works
- Building
- Finishing works / Craftsmanship
- Heavy industry
- Light industry
- Maintenance

Certifications and norms



EN 388
3 3 4 3 D P

ANSI ISEA 105

A4

Protects against risks



Shock



Cutting



enjoy safety

Edit 30/11/2024
www.deltaplus.eu



Hand protection

EOS NOCUT VV909

LONG-LASTING CUT WORK

Impact glove for heavy work, with high flexibility and lightness thanks to its PVC reinforcements made like honeycomb

Standards - Details



EN388:2016+A1:2018

3 [0-4] ABRASION RESISTANCE
3 [0-5] CUT RESISTANCE
4 [0-4] TEAR RESISTANCE
3 [0-4] PIERCE RESISTANCE
D [A-F] CUT RESISTANCE ISO 13997
P [P] IMPACT RESISTANCE (OPTIONAL)

Technical details

Glove kind	Special glove
Glove family	Knitted coated glove
Mechanical glove kind	Knitted
Special gloves kind	Impact
Coating material and finition	Nitrile foam
Coating level	Palm coated
Number of layer	Single layer
Gauge	13
Benefits element	Reach, Vendor pack
Color	Yellow-Grey-Black
Size	8, 9, 10, 11
Type of packaging	Header card








Safety gloves

EOS NOCUT VV909

LONG-LASTING CUT WORK

Impact glove for heavy work, with high flexibility and lightness thanks to its PVC reinforcements made like honeycomb

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
VV909JA08	Yellow-Grey-Black	08	EOS NOCUT VV909	3295249297107	13295249297104	60	12	9.2 kg	34.6 cm	71.0 cm	18.6 cm
VV909JA09	Yellow-Grey-Black	09	EOS NOCUT VV909	3295249297114	13295249297111	60	12	9.5 kg	34.4 cm	71.8 cm	18.8 cm
VV909JA10	Yellow-Grey-Black	10	EOS NOCUT VV909	3295249297121	13295249297128	60	12	10.6 kg	36.6 cm	74.8 cm	19.4 cm
VV909JA11	Yellow-Grey-Black	11	EOS NOCUT VV909	3295249297138	13295249297135	60	12	10.9 kg	36.4 cm	75.6 cm	18.6 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height