

# APH-HV-M - Cover profile carrier

1136699

<https://www.phoenixcontact.com/gb/products/1136699>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cover profile carrier, Middle piece for attaching the AP-BTO 5,5/14 cover profile, material: PA, color: gray

## Your advantages

- For attaching to HV M12/1-TP or HV M12/2-TP partition plate
- Height can be adjusted by removing intermediate areas

## Commercial data

Item number	1136699
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BE4113
Product key	BE4Z1X
GTIN	4063151073015
Weight per piece (including packing)	3.712 g
Weight per piece (excluding packing)	3.67 g
Country of origin	CN

# APH-HV-M - Cover profile carrier

1136699

<https://www.phoenixcontact.com/gb/products/1136699>



## Technical data

### Notes

Assembly note	Middle piece for attaching the AP-BTO 5,5/14 cover profile
---------------	--

### Product properties

Product type	Cover profile carrier
--------------	-----------------------

### Dimensions

Width	4.5 mm
Height	50.2 mm
Depth	35 mm
Length	50.2 mm

### Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V2

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

# APH-HV-M - Cover profile carrier

1136699

<https://www.phoenixcontact.com/gb/products/1136699>



## Classifications

### ECLASS

ECLASS-12.0	27141135
ECLASS-13.0	27250302

### ETIM

ETIM 9.0	EC001041
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# APH-HV-M - Cover profile carrier

1136699

<https://www.phoenixcontact.com/gb/products/1136699>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)