

FEATURES

- The high-quality nitrile synthetic rubber offers softness and comfort, that is easy to put on with a smooth finish for a perfect fit
- Textured fingertips provide extra grip, to prevent the risk of dropping equipment or slipping when using fragile objects, even when working with liquids
- Each disposable glove has been designed for durability to protect the hand from a wide array of chemical hazards, solvents and oils, as well as reducing the risk of contamination from skin contact to ensure the highest levels of hygiene
- A powder free coating on the inner surface of each glove ensures that the gloves are secure from any potential dust contamination
- Added strength and protection at the cuff prevents the glove from being damaged easily when being put on and offers reliable protection at the weakest point
- These gloves are latex free so are suitable for latex allergy sufferers
- Available in a variety of sizes - Small, Medium, Large and Extra Large
- 100 disposable gloves per pack

RS PRO Disposable Gloves - Blue Nitrile Disposable Gloves

RS Stock No.: 1846039



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Powder Free Disposable Nitrile Gloves

Introducing the RS PRO Powder Free Disposable Nitrile Gloves. These high-quality disposable gloves offer strength, durability and barrier protection that prevents skin contact to ensure contamination does not occur. They have been designed for maximum sensitivity, dexterity and comfort, and offer increased elasticity and flexibility to reduce the risk of fatigue when in use for extended periods of time. These RS PRO nitrile gloves are an essential piece of PPE (Personal Protective Equipment) and allow the wearer to use the gloves at ease and with additional reassurance that they are protected.

General Specifications




Glove Type	Chemical Resistant, Medical
Glove Size	8 - M
Glove Material	Nitrile
Colour	Blue
Food Safe	YES
Powdered	Powder-Free
Grip Design	Textured
Number Of Gloves	100

Electrical Specifications

Anti-Static	NO
--------------------	-----------

Approvals

European Safety Standard	EN 455 Part 1 & 2 EN ISO 374-1:2016 Type C (K > 480 mins) CE Food Safe
---------------------------------	--

<p>EN 374</p>  <p>Protection from chemical risks</p>	<p>EN 1186</p>  <p>Protection for contact with food</p>	<p>ISO 374-5:2016</p>  <p>VIRUS</p> <p>Protection from bacteria and fungi</p>
<p><input type="radio"/> DIN EN 374- Type A</p> <p><input type="radio"/> DIN EN 374- Type B</p> <p><input checked="" type="radio"/> DIN EN 374- Type C</p>	<p><input type="checkbox"/> DIN EN 1186</p>	<p><input type="checkbox"/> DIN EN 374-5:2016</p>

Similar Products

Stock No.	Brand	Product Name	Glove Type	Glove Size	Glove Material
1846039	RS PRO	Blue Nitrile Disposable Gloves	Chemical Resistant, Medical	8 - M	Nitrile
1846040	RS PRO	Blue Nitrile Disposable Gloves	Chemical Resistant, Medical	9 - L	Nitrile