

7-Port Industrial USB 10Gbps Hub with Power Adapter, Metal, Mountable, 5x USB-A and 2x USB-C Downstream Ports, ESD Protection, Powered USB Hub, TAA

Product ID: HB31C5A2CME



The 7-Port Industrial USB 10Gbps Hub with Power Adapter features 5x USB-A and 2x USB-C device ports. Built with a durable all-metal enclosure, it withstands harsh and industrial environments while offering Level-4 Electrostatic Discharge (ESD) protection (15kV Air / 8kV Contact) to safeguard connected devices. For secure connections, this hub includes two 3.3ft (1m) USB cables (USB-C to C & USB-C to A) with side screw locking to prevent accidental disconnection. The hub can be surface-mounted (on or under a desk, wall-mounted) or DIN rail-mounted, ensuring a secure and space-efficient installation.

This versatile hub can be powered via the included universal power adapter or the 7-24V DC terminal block, making it ideal for industrial settings or where standard power outlets may be limited.

When not connected to a host, the hub functions as a dedicated charging station, supporting BC1.2 charging / Dedicated Charging Port (DCP) across all ports. Each port delivers up to 2.4A, with a total power budget of 40W (8A) when all ports are in use, ensuring efficient charging for multiple high-powered peripherals.

With speeds of up to 10Gbps on all downstream ports, this hub is ideal for data storage banks, SSDs, NVMe enclosures, RAID drive enclosures, and 3D printers/scanners. It is fully backwards compatible with USB 3.2 Gen 1 (5Gbps), USB 2.0, and USB 1.x devices.

This TAA Compliant hub is compatible with all operating systems and host devices and has been tested for compatibility with Windows, macOS, Linux, and ChromeOS.

Certifications, Reports and Compatibility





Applications

Features

- **7-PORT INDUSTRIAL USB HUB:** Plug-and-play USB 3.2 Gen 2 hub with durable metal housing, ideal for harsh environments; Features 5x USB-A plus 2x USB-C ports with 10Gbps shared bandwidth, ESD Protection (15kV air/8kV contact) and 350W surge protection
- **VERSATILE MOUNTING:** Securely install on or under a desk, wall, or DIN rail with built-in mounting ears and included DIN clips; Includes two 3.3ft (1m) USB-C to C/USB-C to A cables with screw lock USB-C host connector to prevent unwanted disconnections
- **HIGH-SPEED DATA TRANSFER:** Achieve speeds up to 10Gbps on all downstream ports, ideal for data storage banks, SSDs, NVMe enclosures, RAID enclosures, 3D printers/scanners, and more; Backwards compatible with USB 3.0 (5Gbps), 2.0 and 1.x
- **POWER AND CHARGE:** Functions as a charging station when not connected to a host; Provides 12W (2.4A) on all ports up to a total 40W draw; Powered via universal adapter (included) or 7-24V DC terminal block
- **COMPATIBILITY:** OS independent and tested for compatibility with Windows/macOS/Linux/ChromeOS; No drivers or software required; USB Event Monitoring Utility available; TAA Compliant

Hardware

Warranty	2 Years
Interface	USB 3.2 Gen 2 / 10Gbps
Bus Type	USB 3.2 Gen 2 10Gbps
Industry Standards	USB 3.0 - Backward compatible with USB 3.0 (5Gbps), 2.0, and 1.x.
Chipset ID	VIA/VLI VL822

Performance

Maximum Data Transfer Rate	10 Gbps (USB 3.2 Gen 2)
Type and Rate	USB 3.2 Gen 2 - 10 Gbit/s
Supported Charging Outputs	BC 1.2 (1.5A)

	MTBF	163,021.7 hours
Connector(s)		
	External Ports	1 - Terminal Block (2 Wire)
Software		
	OS Compatibility	OS Independent; No additional drivers or software required
Indicators		
	LED Indicators	7 - USB Port Status LEDs: Solid Green - USB Peripheral is Connected Off - USB Peripheral is Not Connected 1 - Power LED Solid Green: USB Hub is receiving power
Power		
	Input Voltage	110V-240V AC
Environmental		
	Operating Temperature	0C to 55C (32F to 131F)
	Storage Temperature	-20C to 85C (-4F to 185F)
	Humidity	5%~95% RH (Non-condensing)
Physical Characteristics		
	Color	Black
	Material	Steel
	Product Length	2.4 in [6.0 cm]
	Product Width	1.0 in [2.6 cm]
	Product Height	7.0 in [17.8 cm]
	Weight of Product	10.6 oz [300 g]
Packaging Information		
	Package Length	7.4 in [18.7 cm]
	Package Width	11.4 in [29.0 cm]

Package Height 2.8 in [7.0 cm]

Shipping (Package) Weight 3.0 lb [1.4 kg]

What's in the Box

Included in Package	1 - USB Hub
	1 - 3.3 ft [1 m] USB-C to USB-C Locking Cable
	1 - 3.3 ft [1 m] USB-A to USB-C Locking Cable
	1 - Universal Terminal Block Power Adapter (NA/JP, UK, EU, ANZ)
	1 - DIN Mounting Kit
	1 - Quick Start Guide

****Product appearance and specifications are subject to change without notice.***