

A-INL-PG48-N-S - Counter nut



1411266

<https://www.phoenixcontact.com/gb/products/1411266>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads Pg48, color: silver-colored



Commercial data

Item number	1411266
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	AF7DZX
Product key	AF7DZX
Catalog page	Page 689 (C-2-2019)
GTIN	4046356923972
Weight per piece (including packing)	34.9 g
Weight per piece (excluding packing)	34.9 g
Customs tariff number	74198090
Country of origin	DE

A-INL-PG48-N-S - Counter nut

1411266


<https://www.phoenixcontact.com/gb/products/1411266>

Technical data

Product properties

Product type	Flat nut
Thread type	Pg48

Dimensions

Dimensional drawing	
Length	5.5 mm
Diameter	59.3 mm
Connecting thread diameter	59.3 mm
Wrench size, counter nut	64 mm
Hexagon angular dimension	69 mm
Thread type connection side	Pg48

Material specifications

Material	Brass, nickel-plated
----------	----------------------

Cable/line

Halogen-free	yes
--------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-70 °C ... 220 °C
---------------------------------	-------------------

A-INL-PG48-N-S - Counter nut


1411266

<https://www.phoenixcontact.com/gb/products/1411266>



Drawings

Dimensional drawing



A-INL-PG48-N-S - Counter nut



1411266

<https://www.phoenixcontact.com/gb/products/1411266>

Classifications

ECLASS

ECLASS-13.0	27140807
-------------	----------

ETIM

ETIM 9.0	EC000879
----------	----------

UNSPSC

UNSPSC 21.0	31161700
-------------	----------

A-INL-PG48-N-S - Counter nut



1411266

<https://www.phoenixcontact.com/gb/products/1411266>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	35dad46d-f96a-4fd1-82ab-4899677536e0

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk