



**PRODUCT NUMBER: 4580381**

**DexPure 803-81**

Thin Nitrile powder-free disposable glove with chemical resistance against contamination and food contact certificate for food industry.

**Honeywell**

**Overview**

**Reference Number**

4580381

**Product Type**

Gloves

**Range**

Chemical Protection

**Line**

Disposable

**Brand**

Honeywell

**Industry**

- Administration
- Aviation
- Catering
- Chemical Industries
- Food Industries
- Services

**Product Use**

Food industry: poultry, fruit & vegetable processing, dairy processing, food distribution, catering

Electronic: precision assembly

Chemical: precision work with non-harmful chemical substances

**Features & Benefits**

**Feature**

Nitrile powder-free disposable glove with violet blue color. 0.07 mm thickness. Food contact certificate together with chemical certificate. Newly designed dispenser box"

**Benefit**

Durable, comfortable as thinner than average chemical disposable gloves, better dexterity for precision work. Food contact certificate and blue color easy to detect makes it suitable for the food industry. It provides protection against non-harmful chemical substances. Latex free. Against risk of Type 1 allergies. New dispenser box design makes it easy to use.

**Technical Description**

**Description**

CE CATEGORY : III Irreversible risks In accordance with STANDARDS : EN 420-2003 EEC Basic standards EN 374-2:2003 & EN 374-3:2003 protection against chemicals and micro-organisms European directive N°1935/2004 : Food contact CHARACTERISTICS : Unpowdered nitrile glove. Violet blue. Single use. Length 24 cm.

**Product Technology**

Dipped glove.

**Glove/liner color**

Violet blue

**Length**

24 cm

**Thickness**

0.07 mm

**Harmlessness**

In conformity with the European standards

**Dexterity**

5

**Sizes**

XS to XL

## Certifications

 E.C. Declaration of Conformity

**EC Attestation**

 AET 4580381- H2

**REACH****EU Regulation 1907/2006 (REACH) Compliance**

The substance(s) listed below may be contained in this product above the threshold level of 0.1% by weight of the listed article.

Product Reference Sold in Europe	Substance > 0.1%
Substance Name	CAS Number
No Substance Content	

## Literature & Documents

08-17-694\_GLOV\_FLY\_Dexpure\_NPI\_GBh

[http://www.honeywellsafety.com/supplementary/documents\\_and\\_downloads/gloves/4294999898/1033.aspx](http://www.honeywellsafety.com/supplementary/documents_and_downloads/gloves/4294999898/1033.aspx)

## Maintenance

**Storage Information**

Minimum packaging : 1 box of 200 gloves.

Cartons of 10 boxes.

Instructions for use printed on the box.

**Care Instructions**

In order to keep its properties, this article should not be cleaned.





In application of the Directive ref. 89/686/EEC of the 21<sup>st</sup> of December 1989, concerning the alignment of member state legislation relating to personal protective equipment and the decrees n° 92-765, 766 and 768 of 29<sup>th</sup> of July 1992 concerning the transposition of this Directive into French law,

## CTC

4,rue Hermann Frenkel - 69367 Cedex 07 - France  
Tel +33 (0)4 72 76 10 10 - Fax +33 (0)4 72 72 76 10 00 - E-Mail : ctclyon@ctcgroupe.com - www.ctc.fr

authorized by decrees of the Ministry of Work, Employment and Health of the 20<sup>th</sup> of December 2010,  
**registered under the number 0075, published in OJEC, delivers :**

<p align="center"><b>EC-TYPE EXAMINATION CERTIFICATE</b> <b>0075/797/162/02/17/0184</b></p>
---

To the following model of personal protective equipment :

- \* reference of the model : 45 803 81
- \* protective glove against low chemical risks
- \* Manufacturer :

**HONEYWELL SAFETY PRODUCT EUROPE**  
Immeuble Edison ZI-Paris Nord II 33, Rue des Vanesses 95 958 ROISSY  
France

Description of the protective glove, reference of technical rules verified in the context of the CE type examination and informations indicated on the product are detailed in the following pages of this certificate.

Drawn up in Lyon, on February 08th, 2017  
**Update 02 of May 29th, 2017**

Issued by Lionel GAUDILLERE



NOTA : Any modification to new items of the personal protective equipment object of this CE type approval certificate or any modification of the information contained in the manufacturer technical file which served for the deliverance of the CE type approval certificate (change of adress, change of company status) should be brought to the attention of the notified body in accordance with law n° R. 4313-38 of the French Code of Work.

## 1. DESCRIPTION OF THE PROTECTIVE GLOVE

According to the technical file index : 03  
 Reference : 45 803 81  
 Basic Model  
 Dated : May 2017

Disposable nitrile protective gloves with very good sensitivity, sizes 6,7,8,9,10

### Available sizes :

6      7      8      9      10

### Visual description :



### Material :

	Color	Material	Gauges	Thickness
PALM	Blue	Nitrile		0,07 mm
BACK	Blue	Nitrile		0,07 mm
CUFF	Blue	Nitrile		0,07 mm

## 2. PROTECTION SCOPE

**Compliance with the essential requirements of the Directive 89/686/EEC has been verified by using following technical rules:**

- \* EN 420:2003+A1:2009                    - General requirements for gloves and test methods
- \* EN 374-2:2003                         - Protection gloves against chemicals and micro-organisms
- \* EN 374-3:2003                         - Protection gloves against chemicals and micro-organisms
  
- \* At the date of certificate the product is in compliance with Annex XVII of REACH regulation (n° 1907/2006 and revisions)
- \* This product is a category III (lethal or irreversible risk).

**References of test reports performed in order to verify the compliance with the requirements of the technical rules :**

Laboratory	CTC	Other
EN 420	L161018679_2 L160712647_1 L160712646_1 L170406561_1 L160712645_1	
EN 388	L160712645_1	
EN 374-2	L161018679_2 L160712647_1 L160712646_1 L160712645_1 L170406562_1	
EN 374-3	L161221233_1 L160712749_1 L160712750_1 L160712751_1 L170406563_1	
OTHER	L161119842_1 L160712721_1	5568/10



**Performance levels offered against chemicals and micro-organisms (EN 374-2:2003) are:**

Protection offered	Performance levels
Water tightness	conform
Air tightness	conform
Quality acceptable level	Level 2 : < 1,5


This glove is considered as micro-organism resistant.

**Performance levels offered against chemicals (EN 374-3:2003) are:**

Name of chemicals	Sodium Hydroxyde 40%					
Letter code of the product	k					
Permeation performance levels	6					

### 3. MARKING

**Each glove is clearly marked with the following information:**

- \* Logo of the authorized representative:
- \*  marking with the number of the notified body in charge of the article 11A of Directive 89/686/CEE / EPI, 0075.
- \* reference of the model: 45 803 81
- \* size
- \* pictogram for chemicals risks and micro-organisms risk
- \* information pictogram

**Marking example:**







# E.C. Declaration of Conformity

**The manufacturer or its legal representative supplier in the European Community:**

Honeywell Safety Products Europe

**Declares that the Personal Protective Equipment described here after conforms to the provisions of the European Council Directive 89/686/CEE:**

Designation: DexPure 803-81

Reference: 4580381

Standard(s):

**This PPE is the object of the below EC examination certificate n°:**

**Delivered by:**

Drawn up in , on the 16/03/2018

**By:**

**Division:** Gloves

ZI Paris Nord II 33, rue des Vanesses BP 50288 95958 Roissy CDG France

Tel: +33 (0) 49 90 79 79 Fax: +33 (0)1 49 90 79 80

[www.honeywellsafety.com](http://www.honeywellsafety.com)

## DexPure® 803-81

Reliability That Comes in Handy.

For workers in the food industry and precision electronic assembly, the new DexPure® 803-81 provides excellent hand protection against non-harmful substances. The single use nitrile gloves are durable and powder-free and provide basic chemical resistance against contamination. They also fit well on any hand, enhancing your dexterity and ensuring full compliance with food processing regulations.




### FEATURES & BENEFITS

- 0.07 mm thick, ensuring dexterity for precision work.
- EN374 compliance, guaranteeing better chemical resistance.
- Superior durability.
- Roughened fingertips for better grip.
- Food contact certificate.
- Free from natural latex.
- Different sizes (XS to XL) for total comfort.
- Packed in dispenser box: newly designed, easy to use.

### TARGET MARKET/APPLICATIONS:

- Food industry: Poultry (chicken processing), Fruit and vegetable processing, Dairy processing, Food distribution, Catering
- Electronic: Precision electronic assembly



### ORDERING INFORMATION

Ref.	Name	Description	Sizes	Packaging
45 803 81	DexPure® 803-81	Nitrile, violet blue, powder-free, AQL 1.5, thickness: 0,07 mm, length: 24 cm	XS to XL	200 pcs / dispenser box

### Honeywell Safety Products

UNITED KINGDOM  
 Honeywell Safety Products UK LTD  
 Phone: +44 (0) 1256 693 200  
 Fax: +44 (0) 1256 693 300  
 Email: info-uk.hsp@honeywell.com

INTERNATIONAL  
 Honeywell Safety Products Europe SAS  
 Phone: +33 (0)1 49 90 79 79  
 Fax: +33 (0)1 49 90 71 04  
 Email: info-export.hsp@honeywell.com

### For more information

[www.honeywellsafety.com](http://www.honeywellsafety.com)

08-17-694 GB - 10/2017  
 ©2017 Honeywell International Inc.