

FR50 - Flame Resistant Anti-Static Coverall 350g

Collection: Bizflame™ Work

Range: Flame Resistant

Shell Fabric: Bizflame Work: 99% Cotton, 1% Carbon Fibre 350g

Product information

This coverall is perfect for the demands of the offshore industry. Constructed with a highly innovative flame-retardant fabric with high visibility reflective tape double stitched for enhanced visibility. Meeting all the required EN standards, features include triple stitched seams, high visibility strips on shoulders, arms and legs, concealed 2-way front brass zip and two front slant chest pockets with concealed brass zips.

Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 2 (A1+A2)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 8.6 CAL/CM²)

IEC 61482-2 IEC 61482-1-2 APC 1

ASTM F1959/F1959M-12 (ATPV=13.6 Cal/CM² (HAF=82%))

Bizflame™ Work

BizFlame™ Work has been developed and designed using a highly innovative flame resistant fabric with added anti-static properties. Constructed from 99% cotton and interwoven with 1% carbon fibres. Excellent tear and tensile strength offer durability while the premium quality cotton fibres give the fabric unrivalled comfort. Inherent anti-static carbon fibre

Flame Resistant

This industry leading flame resistant range provides multi standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Features

- Protection against radiant, convective and contact heat
- Class 2 welding protection
- Rule pocket
- Two back patch pockets
- Hook and loop cuffs for a secure fit
- Action back for extra freedom of movement



FR50 - Flame Resistant Anti-Static Coverall 350g Commodity Code: 6211321000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
Bracetown Business Park
D15 YN2P, Ireland
Cert No: 2777/13136-02/E00-00

OETI (Institut fuer Oekologie, Technik und Innovation GmbH) (Notified Body No.: 0534)
Sebenhirtenstrasse 12A
1230, Austria
Contact: Marion Pfeiler
Cert No: 0598

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	DUN14
FR50BKRS	Black	43.0	28.0	50.0	1.5700	0.0602	5036108284054	15036108774248
FR50BKRM	Black	43.0	28.0	50.0	1.6000	0.0602	5036108284047	15036108774231
FR50BKRL	Black	43.0	28.0	50.0	1.5600	0.0602	5036108284030	15036108774224
FR50BKRXL	Black	43.0	28.0	50.0	1.6600	0.0602	5036108284061	15036108774255
FR50BKRXXL	Black	43.0	28.0	55.0	1.8600	0.0662	5036108284078	15036108774262