




DELTA pushbutton device insert, UP with continuous lighting 1 NO, with N terminal without claws 10A 250V

| Model                            |                                 |
|----------------------------------|---------------------------------|
| product brand name               | DELTA                           |
| product designation              | Pushbutton insert               |
| design of the product            | single pushbutton               |
| design of the switching function | others                          |
| type of composition              | base element                    |
| design of the actuating element  | pushbutton/momentary pushbutton |
| General technical data           |                                 |
| printed marking                  | Without                         |
| mounting type                    | flush mounting                  |
| surface processing               | others                          |
| material                         | others                          |
| Supply voltage                   |                                 |
| operating voltage rated value    | 250 V                           |
| Protection class                 |                                 |
| protection class IP              | IP20                            |
| Breaking Capacity                |                                 |
| switching capacity current       | 10 A                            |
| Main circuit                     |                                 |
| operational current rated value  | 10 A                            |
| Appearance                       |                                 |
| appearance                       | not applicable                  |
| color                            | miscellaneous                   |
| Product details                  |                                 |
| product component                |                                 |
| • labeling field                 | No                              |
| • integrated light source        | No                              |
| • signaling contact              | No                              |
| number of NC contacts            | 0                               |
| number of NO contacts            | 1                               |
| number of CO contacts            | 0                               |
| product feature                  |                                 |
| • halogen-free                   | Yes                             |
| • transparent                    | No                              |
| Number                           |                                 |
| number of actuating rockers      | 1                               |
| Mechanical Design                |                                 |
| height                           | 70 mm                           |
| width                            | 70 mm                           |
| depth                            | 32 mm                           |

|                                                        |              |
|--------------------------------------------------------|--------------|
| fastening method                                       | screw fixing |
| material of the enclosure                              | metal        |
| <b>Environmental footprint</b>                         |              |
| Environmental Product Declaration (EPD)                | Yes          |
| global warming potential [CO2 eq] total                | 4.86 kg      |
| global warming potential [CO2 eq] during manufacturing | 0.353 kg     |
| global warming potential [CO2 eq] during operation     | 4.49 kg      |
| global warming potential [CO2 eq] after end of life    | 0.016 kg     |
| <b>Approvals Certificates</b>                          |              |
| General Product Approval                               | other        |
| Environment                                            |              |



[Confirmation](#)



#### Further information

##### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TD2116-0KK>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TD2116-0KK>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5TD2116-0KK](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TD2116-0KK)

##### CAX-Online-Generator

<http://www.siemens.com/cax>

##### Tender specifications

<http://www.siemens.com/specifications>



last modified:

4/4/2025 

