

PRODUCT-DETAILS

# TY25M

## CABLE TIE 50LB 7IN NATURAL NYLON




---

### General Information

Extended Product Type	TY25M
Product ID	7TAG009210R0042
EAN	5414363062448
Catalog Description	CABLE TIE 50LB 7IN NATURAL NYLON
Long Description	High Performance Cable Tie for Indoor applications, Natural Color Nylon 6.6, Length of 186mm (7.3 Inches) for Bundle Diameter up to 48mm (1.89 Inches), Width of 4.67mm (0.184 Inch), Tensile Strength Rating of 220 Newtons (50 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), UL/EN/CSA62275 Type 2/215 Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Bulk Pack

---

### Ordering

EAN	5414363062448
Customs Tariff Number	3926909990

---

### Dimensions

Product Net Weight	.002 lb .907 g
--------------------	-------------------

---

### Container Information

Package Level 1 Units	1000 piece
-----------------------	------------

Package Level 1 Width	9.85 in 250 mm
Package Level 1 Height	3.65 in 93 mm
Package Level 1 Depth / Length	13.55 in 344 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	13.5 in 343 mm
Package Level 2 Height	9.7 in 246 mm
Package Level 2 Depth / Length	21 in 533 mm

## Additional Information

Brand / Label	Ty-Rap
Bundle Diameter	0.138 to 1.77 in 3.5 to 45 mm
Color	Natural
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	PLASTIC CABLE TIE
Product Type	High Performance
Special Functions	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Standards	UL E49405, CSA 2884
Tensile Strength	50 lb 222 N
Thickness	0.043 in 1.09 mm
UPC	786210824574

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY25M
Declaration of Conformity - CE	9AKK107492A9841
Instructions and Manuals	TY25M

## Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

---

## Categories

---

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

