


BW 2400S 7/E-M Mobile roller cab with 7 drawers, with assortment of 309 tools

- 7 drawers (588x367 mm), with ball bearing slides:
- 5 drawers, 70 mm high
- 1 drawer, 140 mm high
- 1 drawer, 210 mm high
- Drawer bases protected by foamed rubber mats
- Four castors Ø 125 mm: 2 fixed and 2 steering (one with brake)
- Front centralized safety lock
- Static load capacity: 800 kg
- Thermoplastic worktop
- Built-in side bottle holder



	Art.
024006324	BW 2400S 7/E-M-O
024006325	BW 2400S 7/E-M-A
024006326	BW 2400S 7/E-M-R

- n. 1 **BW 32:** Centre punches Ø 4 mm
- n. 1 **BW 34:** Flat chisels 150 mm
- n. 1 **BW 36:** Cape chisels 150 mm
- n. 1 **BW 1048:** Slip joint pliers, boxed joints 250 mm
- n. 1 **BW 1082BM:** Diagonal cutting nippers □ □ 160 mm
- n. 1 **BW 1150BM:** Heavy-duty combination pliers □ □ 180 mm
- n. 1 **BW 1166BM:** Extra-long needle knurled nose pliers □ □ 200 mm
- n. 1 **BW 1370:** Engineer's hammers □ 500 g
- n. 1 **BW 1390:** Soft face hammer, plastic faces Ø 35 mm
- n. 9 **BW 96BPC/SC9:** Set of 9 ball head offset hexagon key wrenches □ □ 1,5-2-2,5-3-4-5-6-8-10 mm
- n. 22 **BW 1256/C21-1:** Micro screwdriver with 21 interchangeable inserts 4 mm and handle □ 4 mm
- n. 13 **BW 900:** Hexagon hand sockets, 1/4" □ □ □ 4-4,5-5-5,5-6-7-8-9-10-11-12-13-14 mm
- n. 13 **BW 900L:** Hexagon hand sockets, long series, 1/4" □ □ □ 4-4,5-5-5,5-6-7-8-9-10-11-12-13-14 mm
- n. 6 **BW 900ME:** Socket drivers for hexagon screws, 1/4" □ □ □ 3-4-5-6-7-8 mm
- n. 8 **BW 900TX:** Socket drivers for Torx® head screws, 1/4" □ □ □ T06-T07-T08-T09-T10-T15-T20-T25
- n. 1 **BW 895/1:** Socket holders for items BW 861, BW 862, BW 866 □ □
- n. 1 **BW 900/20:** Extension cords - 1/4" 50 mm
- n. 1 **BW 900/20L:** Extension cords - 1/4" 100 mm
- n. 1 **BW 900/25:** Universal joint - 1/4"
- n. 1 **BW 900/30:** 1/4" drive spinner handle 150 mm
- n. 1 **BW 900/42:** 1/4" drive sliding T-handle 115 mm
- n. 1 **BW 900/55:** Reversible ratchet, 1/4" □ □ 150 mm
- n. 2 **BW 910/16F:** Adaptor - F3/8"xM1/2" E 3/8" - B1/2"
- n. 20 **BW 920A:** Hexagon hand sockets, 1/2" □ □ □ 8-9-10-11-12-13-14-15-16-17-18-19-20-21-22-23-24-27-30-32 mm
- n. 8 **BW 920PE:** Socket drivers for hexagon screws, 1/2" □ □ □ 5-6-7-8-9-10-12-14 mm
- n. 7 **BW 920TX:** Socket drivers for Torx® head screws, 1/2" □ □ □ T27-T30-T40-T45-T50-T55-T60
- n. 11 **BW 920AL:** Hexagon hand sockets, long series, 1/2" □ □ □ 10-12-13-14-15-16-17-18-19-21-22 mm
- n. 1 **BW 920/21:** Extension bar - 1/2" 125 mm
- n. 1 **BW 920/22:** Extension bar - 1/2" 250 mm
- n. 1 **BW 920/25:** Universal joint, 1/2"
- n. 8 **BW 55:** Double open end wrenches □ 6x7-8x9-10x11-12x13-14x15-16x17-18x19-20x22 mm



Scan the QR Code to access the web tab

Specs, media and documentation in one click.

