

# HC-CIF-BFFD-HI-FH-AL - DIN rail mounting frame



1518648

<https://www.phoenixcontact.com/gb/products/1518648>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail mounting frame, design: B24, base frame, material: die-cast aluminum, uncoated, 180° hinged, for top frame HC-CIF-B24-HFFD..., for DIN rails NS 35/7.5

## Your advantages

- Stable metal version
- Open base, pre-assembled cable harnesses can be used
- Safe leading PE even when plugged in at a slight angle and independent of the installation direction
- Particularly easy to access due to the innovative 180° swivel mechanism

## Commercial data

Item number	1518648
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AF7AHB
Product key	AF7AHB
GTIN	4063151982621
Weight per piece (including packing)	232.2 g
Weight per piece (excluding packing)	22.22 g
Country of origin	PL

# HC-CIF-BFFD-HI-FH-AL - DIN rail mounting frame



1518648


<https://www.phoenixcontact.com/gb/products/1518648>

## Technical data

### Product properties

Product type	DIN rail mounting frame
Housing type	DIN rail mounting frame
Series	HC-CIF-AL
Type	B24
Protective cover	no
Pg screw connection	none

### Dimensions

Dimensional drawing	
Width	56 mm
Height	125 mm
Length	145 mm

### Material specifications

Housing material	Cast aluminum, uncoated
------------------	-------------------------

### Mechanical properties

#### Mechanical data

Locking type	Nut
--------------	-----

### Mounting

Mounting type	DIN rail: 35 mm
Assembly note	When using an aluminum DIN rail, the freedom of movement of the DIN rail mounting frame is restricted so that continuous vibration does not lead to excessive strain on the DIN rail. This can be achieved by using additional end brackets next to the DIN rail mounting frame.


# HC-CIF-BFFD-HI-FH-AL - DIN rail mounting frame

1518648

<https://www.phoenixcontact.com/gb/products/1518648>



## Drawings



# HC-CIF-BFFD-HI-FH-AL - DIN rail mounting frame



1518648

<https://www.phoenixcontact.com/gb/products/1518648>

## Classifications

### ECLASS

ECLASS-13.0	27440210
-------------	----------

### ETIM

ETIM 9.0	EC002310
----------	----------

# HC-CIF-BFFD-HI-FH-AL - DIN rail mounting frame



1518648

<https://www.phoenixcontact.com/gb/products/1518648>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)