

KDT-ST 7 - Filler plug

3063963

<https://www.phoenixcontact.com/gb/products/3063963>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Filler plug, material: PA, length: 25 mm, diameter: 7 mm



Commercial data

Item number	3063963
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	AF7CZX
Product key	AF7CZX
Catalog page	Page 682 (C-2-2019)
GTIN	4046356301428
Weight per piece (including packing)	0.925 g
Weight per piece (excluding packing)	0.9 g
Customs tariff number	39174000
Country of origin	DE

KDT-ST 7 - Filler plug

3063963

<https://www.phoenixcontact.com/gb/products/3063963>



Technical data


Notes

General	The filler plugs are used to seal unused cable sleeves.
---------	---

Product properties

Product type	Sealing plugs
--------------	---------------

Dimensions

Dimensional drawing	
Length	25 mm
Diameter	7 mm

Material specifications

Color	black (RAL 9005)
Material	PA

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP54 (Observe the assembly instructions)
Ambient temperature (operation)	-20 °C ... 80 °C

Mounting

Assembly note	IP54: for vertical sealing frame mounting/for horizontal sealing frame mounting (downward cable outlet direction).
---------------	--

KDT-ST 7 - Filler plug



3063963

<https://www.phoenixcontact.com/gb/products/3063963>



Drawings

Dimensional drawing



Dimensional drawing

KDT-ST 7 - Filler plug

3063963

<https://www.phoenixcontact.com/gb/products/3063963>



Classifications

ECLASS

ECLASS-13.0	23111190
-------------	----------

ETIM

ETIM 9.0	EC000032
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

KDT-ST 7 - Filler plug

3063963

<https://www.phoenixcontact.com/gb/products/3063963>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk