

# Wiha magazine bit holder.

Eight screwdrivers in one.

## Magazine bit holder 1/4", magnetic.



### 38090101 Magazine bit holder, magnetic, 1/4".

Blade: High grade chrome-vanadium steel, through hardened.  
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.  
 Bit holder: Stainless steel with strong magnet.  
 Suitable for: DIN 3126, ISO 1173, style D 6.3.  
 Bits: 25 mm Standard bits.  
 Application: The alternative to a screwdriver set.  
 Eight drive shapes in one screwdriver.

Order-No.	Series	
32901 3	38090101	5
⓪	7010 Z	1x6.5
⊕	7011 Z	1xPH1 1xPH2 1xPH3
⊕	7012 Z	1xPZ2
⊕	7015 Z	1xT15 1xT20 1xT25

### SB 38090101 Magazine bit holder, magnetic, 1/4". Blister packed.

Order-No.	Series	
33007 1	SB 38090101	5



### 38090101 VH Magazine bit holder, display, 10 pcs. Sales display made of card with integrated rear panel.

Order-No.	Series-No.	Content	
33244 0	38090101 VH	10 x 38090101	⓪ ⊕ ⊕ ⊕ 1
33245 7	38090102 VH	10 x 38090102	⊕ 1
33246 4	38090103 VH	10 x 38090103	⓪ ⊕ 1
33247 1	38090104 VH	10 x 38090104	⓪ ⊕ 1

## Magazine bit holder 1/4", magnetic.



### 38090102 Magazine bit holder, magnetic, 1/4".

Order-No.	Series	
32902 0	38090102	5
⊕	7015 Z	1xT6 1xT8 1xT10 1xT15 1xT20 1xT25 1xT30 1xT40

### SB 38090102 Magazine bit holder, magnetic, 1/4". Blister packed.

Order-No.	Series	
33008 8	SB 38090102	5
⊕	7015 Z	1xT6 1xT8 1xT10 1xT15 1xT20 1xT25 1xT30 1xT40



### 38090103 Magazine bit holder, magnetic, 1/4".

Order-No.	Series	
32903 7	38090103	5
⓪	7010 Z	1x5,5 1x6,5
⊕	7011 Z	1xPH1 3xPH2 2xPH3

### SB 38090103 Magazine bit holder, magnetic, 1/4". Blister packed.

Order-No.	Series	
33009 5	SB 38090103	5
⓪	7010 Z	1x5,5 1x6,5
⊕	7011 Z	1xPH1 3xPH2 2xPH3



### 38090104 Magazine bit holder, magnetic, 1/4".

Order-No.	Series	
32904 4	38090104	5
⓪	7010 Z	1x5,5 1x6,5
⊕	7012 Z	1xPZ1 3xPZ2 2xPZ3

### SB 38090104 Magazine bit holder, magnetic, 1/4". Blister packed.

Order-No.	Series	
33010 1	SB 38090104	5
⓪	7010 Z	1x5,5 1x6,5
⊕	7012 Z	1xPZ1 3xPZ2 2xPZ3

# Wiha magazine bit holder Stubby.

The Stubby with six bits in its cap.

## Magazine bit holder 1/4", magnetic.



### 380101 Magazine bit holder Stubby, magnetic, 1/4".

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.  
 Bit holder: Stainless steel with strong magnet.  
 Suitable for: DIN 3126, ISO 1173, style D 6.3.  
 Bits: 25 mm Standard bits.  
 Application: The alternative to a screwdriver set.  
 Six drive shapes in one screwdriver.  
 For working in confined spaces.

Order-No.	Series	
33736 0	380101	10
⓪	7010 Z	1x4.5 1x6.5 1x8.0
⊕	7011 Z	1xPH1 1xPH2 1xPH3

### SB 380101 Magazine bit holder Stubby, magnetic, 1/4". Blister packed.

Order-No.	Series	
33738 4	SB 380101	10
⓪	7010 Z	1x4.5 1x6.5 1x8.0
⊕	7011 Z	1xPH1 1xPH2 1xPH3



### 380101 VH Magazine bit holder Stubby, display, 10 pcs. Sales display made of card with integrated rear panel.

Order-No.	Series-No.	Content	
33739 1	380101 VH	10 x 380101	⓪ ⊕ 1
33742 1	380102 VH	10 x 380102	⊕ ⊕ 1
33745 2	380103 VH	10 x 380103	⊕ 1
33747 6	380104 VH	10 x 380104	⓪ ⊕ 1

## Magazine bit holder 1/4", magnetic.



### 380102 Magazine bit holder Stubby, magnetic, 1/4".

Order-No.	Series	
33740 7	380102	10
⊕	7011 Z	1xPH1 1xPH2 1xPH3
⊕	7012 Z	1xPZ1 1xPZ2 1xPZ3

### SB 380102 Magazine bit holder Stubby, magnetic, 1/4". Blister packed.

Order-No.	Series	
33741 4	SB 380102	10
⊕	7011 Z	1xPH1 1xPH2 1xPH3
⊕	7012 Z	1xPZ1 1xPZ2 1xPZ3



### 380103 Magazine bit holder Stubby, magnetic, 1/4".

Order-No.	Series	
33743 8	380103	10
⊕	7015 Z	1xT10 1xT15 1xT20 1xT25 1xT30 1xT40

### SB 380103 Magazine bit holder Stubby, magnetic, 1/4". Blister packed.

Order-No.	Series	
33744 5	SB 380103	10
⊕	7015 Z	1xT10 1xT15 1xT20 1xT25 1xT30 1xT40



### 380104 Magazine bit holder Stubby, magnetic, 1/4".

Order-No.	Series	
33764 3	380104	10
⓪	7010 Z	1x4.5 1x6.5 1x8.0
⊕	7012 Z	1xPZ1 1xPZ2 1xPZ3

### SB 380104 Magazine bit holder Stubby, magnetic, 1/4". Blister packed.

Order-No.	Series	
33746 9	SB 380104	10
⓪	7010 Z	1x4.5 1x6.5 1x8.0
⊕	7012 Z	1xPZ1 1xPZ2 1xPZ3