

Previously known as: Winter Monkey Grip® 23-191



Cold



Heavy Duty

Versatile, heavy-duty work gloves, ensuring warm, dry hand protection in cold conditions

- **Enhanced durability:** ActivArm® 23-191 durable work gloves are not only cut out for extended wear in abrasive conditions, but are ideal for wet and oily low-temperature environments, with optimal grip performance for heavy-duty handling
- **Increased comfort:** These PVC-coated insulated work gloves also provide warm, dry comfort, thanks to their foam insulation
- **Optimized agility:** Anatomically designed for challenging tasks, ActivArm® 23-191 safety gloves ensure a particularly secure fit around the fingers, enabling ease of movement and preventing hand fatigue
- **Certified cold resistance:** These heavy-duty work gloves also satisfy EN 511-111 cold contact standards, for reliable hand protection at low temperatures



Industries

- Metal fabrication

Applications

- Handling materials with sharp or rough edges
- Fabricating metal parts, glass sheets
- Production line support & maintenance
- Equipment repair & maintenance
- Assembly and disassembly of equipment

Previously known as: Winter Monkey Grip® 23-191

Key Features

- **PVC coating:** Protecting hands from abrasion, water, oil and grease
- **Foam insulation:** For breathable work gloves ensuring warm, dry hands
- **Curved fingers, wing thumb and jersey cotton liner:** Greater dexterity

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm Winter Monkey Grip® 23-191	Finishing: Smooth Coating Material: PVC Liner Material: Cotton Jersey Cuff Style: Knitwrist		10, 11	275-290 mm, 11"-12"	Orange	12 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699